

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [50-84-2152](#)
Status: **Active**
Overview: MLX™ Power Connectors
Description: 2.13mm Diameter MLX™ Pin and Socket Receptacle, 15 Circuits

Documents:
[3D Model](#) [Product Specification PS-42022-0001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR19980
UL E29179

General

Product Family Crimp Housings
Series [42022](#)
Application Power, Wire-to-Wire
Comments Glow Wire Equivalent Part Number [366440008](#). Current – Maximum per contact 20A if used with [36663](#) and [36664](#) terminal
Overview [MLX™ Power Connectors](#)
Product Name MLX™
UPC 800754387071

Physical

Circuits (maximum) 15
Circuits Detail 15
Color - Resin Natural
Flammability 94V-0
Gender Female
Glow-Wire Compliant No
Keying to Mating Part None
Lock to Mating Part Yes
Material - Resin Nylon
Net Weight 10.969/g
Number of Rows 3
Packaging Type Carton
Panel Mount Yes
Pitch - Mating Interface 6.35mm
Polarized to Mating Part Yes
Stackable No
Temperature Range - Operating -55°C to +105°C

Electrical

Current - Maximum per Contact 20A

Material Info

Old Part Number 4202215CWHT

Reference - Drawing Numbers

Product Specification PS-42022-0001
Sales Drawing SD-42022-**



EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[42022Series](#)

Mates With
[42021](#) MLX™ Power Crimp Housing Plug

Use With
MLX Crimp Terminal [42023](#) , [42024](#)