


## Dimensions: mm (In.)

**Electrical Specifications:**

- Contact resistance: 100m $\Omega$  max.
- Insulation resistance: 100M $\Omega$  min. @ 500VDC
- Dielectric strength: 250VAC for 1 minute
- Rating: 50mA/12VDC

**Mechanical Specifications:**

- Life: 100,000 cycles
- Operating force: 160 $\pm$ 50gf
- Operation temperature: -25 $^{\circ}$ ~+70 $^{\circ}$ C
- Storage temperature: -30 $^{\circ}$ ~+80 $^{\circ}$ C
- Travel: .010 $\pm$ .001 (.25  $\pm$  .02)
- Stop strength: 3Kg for 15 seconds

**Materials:**

- Cover: stainless steel
- Contacts: silver clad phosphor bronze
- Terminals: silver clad brass
- Base: PPA, black

**Soldering Process:**

- Wave soldering temperature: 260 $^{\circ}$ C max. for 5 seconds
- These switches are washable. They can only be submersed after they have been soldered and returned to normal temperature.

**Tactile Switch**  
101-0265

**Mountain**  
**Switch**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[101-0265](#)