



Self-Laminating Labels for Wire and Cable

- Vinyl material with white print-on area
- Clear overlamine protects legend
- Print with LS6-RWBLK wax ribbon




Part Number	Label Width x Height A x B In. (mm)	Print-On Height C In. (mm)	Nominal Cable Diameter Range In. (mm)	Typical UTP Cable	Typical Fiber Optic Cable	Typical Electrical (THHN)	Labels/ Roll	Std. Pkg. Qty.*	Std. Ctn. Qty.
TWS-6V	0.50 x 0.75 (12.7 x 19.1)	0.38 (9.5)	0.12 (3.1)	—	—	12 AWG	500	1 Roll	10 Rolls
TWS-7V	1.00 x 0.75 (25.4 x 19.1)	0.38 (9.5)	0.12 (3.1)	—	—	12 AWG	250		
TWS-4V	0.50 x 1.00 (12.7 x 25.4)	0.38 (9.5)	0.12 - 0.20 (3.1 - 5.0)	—	2-4 Strand	12-10 AWG	400		
TWS-5V	1.00 x 1.00 (25.4 x 25.4)	0.38 (9.5)	0.12 - 0.20 (3.1 - 5.0)	—	2-4 Strand	12-10 AWG	250		
TWS-1V	0.50 x 1.25 (12.7 x 31.8)	0.50 (12.7)	0.16 - 0.24 (4.0 - 6.1)	4 Pair	2-8 Strand	8 AWG	350		
TWS-2V	1.00 x 1.25 (25.4 x 31.8)	0.50 (12.7)	0.16 - 0.24 (4.0 - 6.1)	4 Pair	2-8 Strand	8 AWG	250		
TWS-3V	1.50 x 1.25 (38.1 x 31.8)	0.50 (12.7)	0.16 - 0.24 (4.0 - 6.1)	4 Pair	2-8 Strand	8 AWG	250		
TWS-40V	2.00 x 1.50 (50.8 x 38.1)	0.50 (12.7)	0.16 - 0.32 (4.0 - 8.1)	4 Pair	2-18 Strand	8-6 AWG	250		
TWS-10V	1.00 x 2.50 (25.4 x 63.5)	0.75 (19.1)	0.24 - 0.56 (6.1 - 14.2)	25 Pair	8-84 Strand	6 AWG-2/0	100		
TWS-11V	1.50 x 2.50 (38.1 x 63.5)	0.75 (19.1)	0.24 - 0.56 (6.1 - 14.2)	25 Pair	8-84 Strand	6 AWG-2/0	100		
TWS-13V	1.50 x 4.00 (38.1 x 101.6)	1.00 (25.4)	0.32 - 0.96 (8.1 - 24.3)	25 Pair	42-156 Strand	4 AWG-500 MCM	100		

* Order number of rolls required in multiples of Std. Pkg. Qty.

Heat Shrink Labels for Wire and Cable

- Flattened Polyolefin Material
- Service Temperature Range: -22°F to 220°F (-30°C to 105°C)
- Shrink Ratio 3:1 @ 212°F (100°C)
- Flammability meets UL Standard 224 for flammability
- Color: White
- Print with LS6-RWBLK wax ribbon



Part Number	Tubing O.D. In. (mm)	Width x Height A x B In. (mm)	Nominal Cable Diameter Range In. (mm)	Typical UTP Cable	Typical Fiber Optic Cable	Typical Electrical (THHN)	Labels/ Roll	Std. Pkg. Qty.*	Std. Ctn. Qty.
THSW-1•	0.13 (3.2)	0.50 x 0.25 (12.7 x 6.4)	0.04 - 0.13 (1.1 - 3.2)	—	—	18-12 AWG	200	1 Roll	10 Rolls
THSW-2	0.13 (3.2)	1.00 x 0.25 (25.4 x 6.4)	0.04 - 0.13 (1.1 - 3.2)	—	—	18-12 AWG	100		
THSW-6•	0.19 (4.8)	0.50 x 0.34 (12.7 x 8.5)	0.06 - 0.19 (1.6 - 4.8)	—	2 Strand	18-10 AWG	200		
THSW-7	0.19 (4.8)	1.00 x 0.34 (25.4 x 8.5)	0.06 - 0.19 (1.6 - 4.8)	—	2 Strand	18-10 AWG	100		
THSW-3•	0.25 (6.4)	0.50 x 0.44 (12.7 x 11.2)	0.08 - 0.25 (2.1 - 6.4)	4 Pair	2-8 Strand	18-8 AWG	200		
THSW-4	0.25 (6.4)	1.00 x 0.44 (25.4 x 11.2)	0.08 - 0.25 (2.1 - 6.4)	4 Pair	2-8 Strand	18-8 AWG	100		
THSW-5	0.50 (12.7)	1.00 x 0.84 (25.4 x 21.3)	0.17 - 0.50 (4.2 - 12.7)	4 Pair	4-60 Strand	8-1 AWG	100		

• Indicates butt-cut style label

*Order number of rolls required in multiples of Std. Pkg. Qty.