

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1120080014](#)
Status: **Active**
Overview: [Network Diagnostics Tools](#)
Description: NetMeter Hand Held DeviceNet Power Monitor, Term. Resistor and Carrying Case

Documents:
[Drawing \(PDF\)](#) [Product Literature \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Field Attachable / Accessories
Series	112008
Approvals	CE, CUL, UL certified
Comments	NetMeter, Power Monitor, Term. Resistor & Bag; Measures 667 Parameters, NetMeter, Power Monitor, Term. Resistor & Bag; Measures 667 Parameters
Communication Speed	125, 250, 500 Kbaud
I/O Connector	5-pole Micro-Change (M12)
IP Rating	N/A
Material - Contact	N/A
Overview	Network Diagnostics Tools
Product Literature Order No	987650-3281
Product Name	DeviceNet, NetMeter
Type	Hand Held Digital NetMeter®
UPC	78172506707
Physical	
Cable Diameter	N/A
Coupling Type	N/A
Diagnostics / LEDs	Yes
Diagnostics Port	Yes
Gender	N/A
Keyway	N/A
Material - Connector Body	N/A
Material - Coupling Nut	N/A
Material - Plating Mating	n/a
Net Weight	343.360/g
Orientation	N/A
Poles	N/A
Temperature Range - Operating	0°C to +40°C
Wire Size AWG	N/A
Electrical	
Current - Maximum per Contact	N/A
Voltage - Maximum	7-30V DC
Material Info	
Engineering Number	DN-MTR-KIT(E)
Reference - Drawing Numbers	
Sales Drawing	E-112008-0014-000



Series image - Reference only

EU ELV Not Relevant	
EU RoHS Not Reviewed REACH SVHC Not Reviewed Halogen-Free Status Not Reviewed For more information, please visit Contact US	China RoHS
China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[112008 Series](#)