



Heavy-Wall Heat-Shrinkable Tubing

T&B Catalog Number:

HSC2-20

UPC Number:

78621087209

Status:

Active

Description:

Heat-Shrinkable HSC Series End Caps for Cable Range 6 - 2 AWG, Expanded Dia. 3/4, Length 2.5 in., rated for 600V, 90 degrees continuous use, Material: Cross-linked polyolefin with thermoplastic adhesive liner, Black

Features

Provides effective method for sealing cable ends, pipe conduit, etc. Extra thickness at the tip of the end prevents sharp ends of the cable from puncturing the seal.

Resistant to common fluids and solvents.

Adhesive liner provides complete environmental protection and insulation.

General

Style	HSC Series End Caps
Color	Black
Temperature Range	-55°C - 110°C
Shrink Ratio	3:1

Dimension Information

Minimum Expanded I.D. (inches)	0.75
Maximum Recovered I.D. (inches)	0.24
Nominal Recovered Wall (inches)	0.09
Cable Range	6 - 2 AWG
Standard Length (inches)	2.5

Specifications

Shrink Temperature	120°C
Voltage Rating	600V
Flammability Rating	UL 94 V-0

Packaging

T&B Order Multiple	10
T&B Inner Pack	10
Package in Units	100
T&B Sold in UOM	Each
T&B Weight Per UOM	2.44 lbs. per 100

Application Support

MSDS Number	msds-0012-tb2msds-0127-tb2
T&B Sales Drawings	wsd-000470
Specifications	Available on Website
Overview	Available on Website

Notes

Order multiple is standard package.

Certifications

RoHS Compliance	No
-----------------	----

Certifications



File Nbr:
E9809