

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


PANDUIT PART NUMBER	STUD SIZE	DIMENSIONS - in.					TOOLS
		A ± .03	W ± .01	C ± .02	M ± .03	H ± .01	
PV6-8RX	#8	1.61 (40.89)	.47 (11.94)	.43 (10.92)	1.37 (34.8)	.17 (4.32)	CT-720 (CD-720PV8-2)
PV6-10RX	#10	1.61 (40.89)	.47 (11.94)	.43 (10.92)	1.37 (34.8)	.20 (5.08)	
PV6-14RX	1/4"	1.61 (40.89)	.47 (11.94)	.43 (10.92)	1.37 (34.8)	.27 (6.86)	
PV6-56RX	5/16"	1.73 (43.94)	.62 (15.75)	.51 (12.95)	1.42 (36.07)	.33 (8.38)	CT-2600 (CD-2600-PV6)
PV6-38RX	3/8"	1.73 (43.94)	.62 (15.75)	.53 (13.46)	1.42 (36.07)	.39 (9.91)	
RV6-12RX	1/2"	1.83 (46.48)	.82 (20.83)	.53 (13.46)	1.42 (36.07)	.52 (13.21)	

NOTES:

- cULus LISTED FOR:
 - 600V MAX VOLTAGE RATING
 - 221° F (105° C) MAX TEMP RATING
 - #6 AWG STRANDED COPPER WIRE
- SEE WWW.PANDUIT.COM FOR PACKAGE QUANTITIES
- MATERIAL:
 - STAMPING - .045" (1.14) THK, COPPER
TIN PLATED
 - HOUSING - VINYL, BLUE
- DIMENSIONS IN BRACKETS ARE IN MILLIMETERS
- WIRE STRIP LENGTH: $7/16 + 1/32$ (11.1 + .8)
- 0 - 0



LISTED
587H
E52164



						TITLE	
						#6 BARREL VINYL INSULATED RING TONGUE .436 [11.07] MAX. WIRE INSUL. DIAMETER	
						CUSTOMER DRAWING	
						ITEM REVISION NAME	PANDUIT
						N41222BB/05	
						DATASET FILE NAME	
						N41222BB/05	MATERIAL: SEE NOTE 3
						UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]	
						.X ± .XXX ± .XX ± ANGLES ±	
						THIRD ANGLE PROJECTION	DRAWING NUMBER: A41222
05	06/14	MBY	JHNU	RGB	REVISED UL LOGO TO cULus LOGO, REVISED NOTES, MOVED TOOLS TO TABLE, UPDATED BORDER	N41222BB-A41222	
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY DAW
							DATE
							CHK
							SCALE NONE
							SHT 1 OF 1
							SIZE A