




SAW Filters for Digital Broadcasting



Part Number	Nominal Center Frequency (fn) (MHz)	System	Insertion Loss (dB)	3dB Bandwidth (MHz)	30dB Bandwidth (MHz)	Attenuation (1) (dB)	Attenuation (2) (dB)
SAFCZ38M9WTAZ00R01	38.912	DAB	25.5 max.	1.25 min.	-	11.0 max.[fn±768kHz]	18.0 min.[fn±944kHz]
SAFJB38M9WTBZ00R10	38.912	DAB	20.0 max.	1.4 min.	2.9 max.	-	-
SAFGP43M7WTAZL0B03	43.75	Digital CATV	21.0 max.	6.0 typ.	-	34.0 min.[39.75MHz]	9.0 min.[40.25MHz]
SAFGP43M7WTGZL0B03	43.75	Digital CATV	29.0 max.	6.1 typ.	-	32.0 min.[39.75MHz]	8.0 min.[40.25MHz]
SAFGP44M0WTGZL0B03	44.00	Digital CATV	21.0 max.	6.1 typ.	-	32.0 min.[40.00MHz]	7.0 min.[40.50MHz]
SAFGP57M0WT0ZL0B03	57.00	Digital CATV	18.0 max.	6.0 typ.	-	30.0 min.[52.75MHz]	3.0 max.[54.19MHz]
SAFGK43M7WTCZL0B03	43.75	Digital TV	21.5 max.	5.4 min.(5.6MHz typ.)	7.5 max.	40.0 min.[39.75MHz]	22.0 min.[40.25MHz]
SAFGK44M0WTCZL0B03	44.00	Digital TV	22.0 max.	5.6 typ.	-	0.7 ±1.3dB[41.31MHz]	1.5 ±1.5dB[46.69MHz]
SAFGM44M0WA0Z00B03	44.00	Interactive TV	20.5 max.	1.7 typ.	-	2.5 ±1.5dB[43.15MHz]	2.0 ±1.5dB[44.85MHz]