







REV.	DESCRIPTION/ECO NO.	DATE
RELEASED		8/83
A	9.0 TO 9.0 MAX.	9/84
B	8.0 TO 8.0±0.1 AND 1.5±.05	1/85
C	TO 1.5±0.1	2/6/98
D	4.5 TO 4.5±0.1	1/1/00
DRAWING CONVERTED TO		
CAD-ADD LAMPS CW1240.		
8111, CW11, CW145		
E	CNW1-7219 C-2F TO C-2V	7/12/00
F	DEGREE DIM. CORRECT. TO 3/14/01	
PC PATTERN		

PC BOARD PUNCH PATTERN

(NO TREATMENT SUCH AS APPLICATION OF FLUX, SHALL BE DONE.)



JKL LAMP NUMBER	VOLTS RATED	AMPS ±10%	*MSCP ±25%	*LUMENS ±25%	AVERAGE LIFE HRS.	FILAMENT TYPE
CNW1-8732	2.5	.100	.100	1.25	10,000	C-2R
CNW1-CW27	5.0	.040	.028	0.35	20,000	C-2R
CNW1-683	5.0	.060	.050	0.63	100,000	C-2R
CNW1-715	5.0	.115	.150	1.89	40,000	C-2R
CNW1-7218	10.0	.027	.100	1.26	10,000	C-2F
CNW1-CW44	12.0	.040	.090	1.13	10,000	C-2F
CNW1-7219	12.0	.060	.150	1.89	16,000	C-2V
CNW1-CW1240	14.0	.040	.120	1.51	16,000	C-2F
CNW1-23	14.0	.040	.150	1.89	16,000	C-2F
CNW1-8111	14.0	.065	.150	1.89	16,000	C-2F
CNW1-CW11	14.0	.065	.200	2.51	10,000	C-2F
CNW1-CW145	14.5	.030	.080	1.00	5,000	C-2F
CNW1-7220	18.0	.026	.150	1.89	16,000	C-2F
CNW1-6838	28.0	.024	.150	1.89	16,000	CC-2F

*LAMP RATED ONLY WITHOUT BASE

METRIC	DIMENSIONS ARE IN MILLIMETERS	TOLERANCE UNLESS OTHERWISE SPECIFIED
THIRD ANGLE PROJECTION	1 PL. +/- .02	2 PL. +/- .020
ANGLE +/- .0		
DRAWN BY L. WENGSTROM	APPROVED BY E. D.	DATE 3/14/01
- CAD DRAWING -		MANUAL REVISIONS NOT PERMITTED
TITLE		SIZE
T-1 NEO-WEDGE BASE WITH MULTIPLE LAMP LISTING		A
SCALE		NONE
DATE		8/83
REVISION		3/14/01
REV. NO. F		SHEET 1 OF 1