




MODEL: BU-P3285

ADAPTER BNC "T" Female-Male-Female



MATERIALS:

Body – Brass, Tarnish resistant plating,
Center Contact – Gold plated beryllium copper
Dielectric – PTFE

RATING:

50 Ohms Impedance
30 VAC/60VDC Max shield/earth
500 VRMS Inner conductor/shield
Temperature: -70°C to 170°C