



TLS 2200®/TLS PC Link™ Label Index By Size (Continued)

Diagram	Catalog Number	Labels Per Roll	Material	Color	B-Number	Label Width Inch (mm) A	Label Height Inch (mm) B	Write-On Height Inch (mm) C	Wire Gauge
1.000" (Continued)									
Fig. 7	PTL-21-427-RD	100	Vinyl	Red	B-427	1.000 (25.4)	2.500 (63.5)	0.750 (19.1)	–
Fig. 7	PTL-21-427-YL	100	Vinyl	Yellow	B-427	1.000 (25.4)	2.500 (63.5)	0.750 (19.1)	–
Fig. 18	PTL-75-461	100	Polyester	White	B-461	1.000 (25.4)	2.625 (66.7)	1.000 (25.4)	–
Fig. 18	BPTL-75-461	1000	Polyester	White	B-461	1.000 (25.4)	2.625 (66.7)	1.000 (25.4)	–
Fig. 18	PTL-75-461-YL	100	Polyester	Yellow	B-461	1.000 (25.4)	2.625 (66.7)	1.000 (25.4)	–
Fig. 18	PTL-75-427	100	Vinyl	White	B-427	1.000 (25.4)	2.625 (66.7)	1.000 (25.4)	–
Fig. 18	PTL-75-461-YL	100	Polyester	Yellow/ Translucent	B-461	1.000 (25.4)	2.625 (66.7)	–	–
Fig. 19	PTL-64-427	100	Vinyl	White	B-427	1.000 (25.4)	3.375 (85.7)	1.125 (28.6)	–
Fig. 19	BPTL-64-427	1000	Vinyl	White	B-427	1.000 (25.4)	3.375 (85.7)	1.125 (28.6)	–
Fig. 19	PTL-64-427	100	Vinyl	White	B-427	1.000 (25.4)	3.375 (85.7)	1.125 (28.6)	–
Fig. 19	BPTL-64-427	1000	Vinyl	White	B-427	1.000 (25.4)	3.375 (85.7)	1.125 (28.6)	–
Fig. 6	PTL-23-499	100	Nylon	White	B-499	1.000 (25.4)	4.000 (101.6)	–	Cables
Fig. 6	PTL-23-498	100	Vinyl	White	B-498	1.000 (25.4)	4.000 (101.6)	–	Cables
Fig. 7	PTL-23-427	100	Vinyl	White	B-427	1.000 (25.4)	4.000 (101.6)	1.000 (25.4)	Cables
Fig. 7	BPTL-23-427	1000	Vinyl	White	B-427	1.000 (25.4)	4.000 (101.6)	1.000 (25.4)	Cables
Fig. 7	PTL-23-427-BL	100	Vinyl	Blue	B-427	1.000 (25.4)	4.000 (101.6)	1.000 (25.4)	Cables
Fig. 7	PTL-23-427-BR	100	Vinyl	Brown	B-427	1.000 (25.4)	4.000 (101.6)	1.000 (25.4)	Cables
Fig. 7	PTL-23-427-GR	100	Vinyl	Green	B-427	1.000 (25.4)	4.000 (101.6)	1.000 (25.4)	Cables
Fig. 7	PTL-23-427-GY	100	Vinyl	Gray	B-427	1.000 (25.4)	4.000 (101.6)	1.000 (25.4)	Cables
Fig. 7	PTL-23-427-OR	100	Vinyl	Orange	B-427	1.000 (25.4)	4.000 (101.6)	1.000 (25.4)	Cables
Fig. 7	PTL-23-427-PL	100	Vinyl	Purple	B-427	1.000 (25.4)	4.000 (101.6)	1.000 (25.4)	Cables
Fig. 7	PTL-23-427-RD	100	Vinyl	Red	B-427	1.000 (25.4)	4.000 (101.6)	1.000 (25.4)	Cables
Fig. 7	PTL-23-427-YL	100	Vinyl	Yellow	B-427	1.000 (25.4)	4.000 (101.6)	1.000 (25.4)	Cables
Fig. 7	PTL-23-427	100	Vinyl	White	B-427	1.000 (25.4)	4.000 (101.6)	1.000 (25.4)	–
Fig. 7	BPTL-23-427	1000	Vinyl	White	B-427	1.000 (25.4)	4.000 (101.6)	1.000 (25.4)	–
Fig. 7	PTL-23-427-BL	100	Vinyl	Blue	B-427	1.000 (25.4)	4.000 (101.6)	1.000 (25.4)	–
Fig. 7	PTL-23-427-BR	100	Vinyl	Brown	B-427	1.000 (25.4)	4.000 (101.6)	1.000 (25.4)	–
Fig. 7	PTL-23-427-GR	100	Vinyl	Green	B-427	1.000 (25.4)	4.000 (101.6)	1.000 (25.4)	–
Fig. 7	PTL-23-427-GY	100	Vinyl	Gray	B-427	1.000 (25.4)	4.000 (101.6)	1.000 (25.4)	–
Fig. 7	PTL-23-427-OR	100	Vinyl	Orange	B-427	1.000 (25.4)	4.000 (101.6)	1.000 (25.4)	–
Fig. 7	PTL-23-427-PL	100	Vinyl	Purple	B-427	1.000 (25.4)	4.000 (101.6)	1.000 (25.4)	–
Fig. 7	PTL-23-427-RD	100	Vinyl	Red	B-427	1.000 (25.4)	4.000 (101.6)	1.000 (25.4)	–
Fig. 7	PTL-23-427-YL	100	Vinyl	Yellow	B-427	1.000 (25.4)	4.000 (101.6)	1.000 (25.4)	–
Fig. 8	PTL-42-422	Continuous	Polyester	White	B-422	1.000 (25.4)	50 ft. (15.2 m)	–	–
Fig. 8	PTL-42-430	Continuous	Polyester	Clear	B-430	1.000 (25.4)	50 ft. (15.2 m)	–	–
Fig. 8	PTL-42-432	Continuous	Polyester	Clear	B-432	1.000 (25.4)	50 ft. (15.2 m)	–	–
Fig. 8	PTL-42-439	Continuous	Vinyl	White	B-439	1.000 (25.4)	50 ft. (15.2 m)	–	–

