Wiha. Premium Tools for Professionals.

# Wiha PicoFinish. The Specialist for Precision Applications.

*The soft material of the handle, together with the rotating cap, enables optimum and sensitive twisting.*

*The clear marking of the drive on the rotating cap provides easy and fast identification of the required screwdriver.*

The Wiha PicoFinish screwdrivers are predestined for high-precision work, predominantly with electro-technical and precision components.

The octagonal rapid-rotation zone at the front of the handle allows rapid twisting.

The extraordinarily easy-to-twist rotating cap permits the delicate turning of fine screws with just one hand.

**PicoFinish Advantages:**

- **Special soft plastic material assures comfortable, delicate work**
- **Ideal for fine adjustments in electronic assembly work and precision applications, as well as for hobby use and model making**
- **Clear marking of the drive on the rotating cap provides easy and fast identification of the required screwdriver**
- **Convex handle end allows the transmission of a controlled high torque to powerfully tighten or loosen the screw head**
- **Palm saving rotating cap with a large surface for the fingers makes incremental adjustment easy**
- **Wiha ChromeTop-finish on tip for a perfect fit every time**





Wiha. Premium Tools
for Professionals.

# Wiha PicoFinish. The Specialist for Precision Applications.

## For Hex Nuts.

**265 P** Nut Driver.

**With rotating cap and rapid-turning zone.**

Blade: Chrome-vanadium steel, through hardened, chrome-plated.
Handle: Wiha PicoFinish handle for rapid rotation.
Application: Ideal for high-precision work with electro-technical and precision components.

| Order-No. | ⌀ | | | | | | | |
|---|---|---|---|---|---|---|---|---|
| 00544 3 | **1.5** | 2.5 | 3.0 | 60 | 160 | 18 | 10 | 310-6202 |
| 00545 0 | **1.8** | 2.9 | 3.5 | 60 | 160 | 18 | 10 | 310-6214 |
| 00546 7 | **2** | 3.2 | 4.0 | 60 | 160 | 18 | 10 | |
| 00547 4 | **2.5** | 4.0 | 4.0 | 60 | 160 | 18 | 10 | 310-6226 |
| 00548 1 | **3** | 5.0 | 5.0 | 60 | 160 | 18 | 10 | 310-6238 |
| 00549 8 | **3.2** | 5.0 | 5.0 | 60 | 160 | 18 | 10 | |
| 00550 4 | **3.5** | 5.3 | 6.0 | 60 | 160 | 18 | 10 | 310-6240 |
| 00551 1 | **4** | 5.5 | 6.0 | 60 | 160 | 18 | 10 | 310-6251 |
| 00552 8 | **4.5** | 6.2 | 7.0 | 60 | 160 | 18 | 10 | 310-6263 |
| 00553 5 | **5** | 6.8 | 7.0 | 60 | 160 | 18 | 10 | 310-6275 |
| 00554 2 | **5.5** | 7.6 | 8.0 | 60 | 160 | 18 | 10 | |
| 00555 9 | **6** | 8.2 | 9.0 | 60 | 160 | 18 | 10 | |
| 00556 6 | **7** | 9.6 | 10.0 | 60 | 160 | 18 | 10 | |

**265 P Zoll** Nut Driver.

**With rotating cap and rapid-turning zone. Inch sizes.**

| Order-No. | ⌀ | | | | |
|---|---|---|---|---|---|
| 00561 0 | **3/32"** | 60 | 160 | 18 | 10 |
| 00564 1 | **7/64"** | 60 | 160 | 18 | 10 |
| 00559 7 | **1/8"** | 60 | 160 | 18 | 10 |
| 00565 8 | **9/64"** | 60 | 160 | 18 | 10 |
| 00562 7 | **5/32"** | 60 | 160 | 18 | 10 |
| 00560 3 | **3/16"** | 60 | 160 | 18 | 10 |
| 00563 4 | **7/32"** | 60 | 160 | 18 | 10 |
| 00558 0 | **1/4"** | 60 | 160 | 18 | 10 |

## Chip Lifter.

**268 10 P** Chip Lifter.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.
Handle: Wiha PicoFinish handle.
Application: For lifting tight parts on circuit boards.

| Order-No. | | | | | | |
|---|---|---|---|---|---|---|
| **00574** 0 | **1** | **3.5** | 50 | 150 | 18 | 5 |