



Bi-Sonic



DC Brushless Fan

433-BP250705H

Date Last Revised: 7-12-06

BI-200007

Dimensions: mm (In.)



Electrical Specifications:

- Insulation resistance: 10meg Ω min. @ 500 VDC
- Dielectric Strength: 5mA max @ 500 VAC 60Hz for 1 min.
- Voltage: 5 VDC
- Operating voltage range: 4.5V - 5.7V
- Rated Current: .12A
- Rated Input Power: 0.60W
- Speed: 12000 R.P.M.
- Max. Air Flow: 2.12 CFM
- Noise: 31 db-A

Mechanical Specifications:

- Operating temperature: -10°C to +70°C

Materials:

- Housing: glass fiber reinforced plastic
- Impeller: PBT are UL 94V-0 rating
- Bearing: Ball

Note:

- RoHS compliant by exemption

Available from Mouser Electronics

1-800-346-6873

www.mouser.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Bi-Sonic:](#)

[BP250705H W-G](#)