

RAFIX 22 QR selector switch, illuminated, round collar, short handle

1.30.242.002/2200

Included: Ring nut with claw.



Other handle marking colours available on request.

General information

Actuator	handle short
Form of collar	round
Marking of handle	white
Colout of front ring	metallized

Dimensions

Overall height	22.2 mm
Width of collar	---
Diameter of collar	29.8 mm
Length of collar	---
Mounting depth with contact block without cable	56.4 mm
Mounting hole	22.3 mm
Key grid	50 x 30 mm

Electrical characteristics

Protection class	II
------------------	----

Mechanical characteristics

Operating force max.	approx. 5 N for 1 switching element
Torque max.	2 Nm

Mechanical design


Mounting	ring nut
Illuminability	yes
Rotating angle	1 x 40°
Contact function	momentary

Other specifications


Ambient temp. operating max.	+70 °C
Ambient temp. operating min.	-25 °C
Resistance to constant environment	according to IEC 600 68-2-3 and 2-30
Storage temperature max.	+80 °C
Storage temperature min.	-40 °C
Operating life	0.5 million
Degree of protection from front side	IP65
Resistance at variable environment	according to IEC 600 68-2-14 and 2-33

16.07.2008

MASS



Frontpanel cut-out



Schaltw

