

EM2795 Series EuroMag Terminal Blocks

Screwless; 5.08 Centers

SPECIFICATIONS

Rating: 10A, 300V

Center Spacing: 0.20" (5.08mm)

Wire Range: #14-24 AWG

Housing Material: UL rated 94V0 Thermoplastic


Contact Material: Tin-Plated Brass

Operating Temperature: 105°C (221°F) max., -40°C (-40°F) min.

Recommended PCB Hole Diameters: 0.051" (1.30mm)


Construction: Mold-to-Length

Agency Information:  File E62622; CE Certified




Dimensions - in (mm)

VERTICAL



HORIZONTAL



Part Numbering System

Series

EM2795

of Positions

02 to 16

Orientation

H - horizontal
V - vertical

To convert to inches, divide by 25.4