



BS,C ,201907,012


C

GEN. ST.	01		02		03		04		05		06		07		08		0D		50		60		70		80		90				
INT. ST.	10	11	12	13	14	18	20	31	32	33	34	38	39	40	42	43	44	45	46	48	56	70	72	73	75	76	81	82	83	84	88

REV.	DATE	DESCRIPTION	BY	C'K'D'
A	14-09-01	CONVERSION REVISION 00	KN	
B	21-11-01	EC B10094	MF	
C	27-11-04	104-0109	ALEX B	BKP



ALIGNMENTSTRIP



PERFORMANCE CHARACTERISTICS


CURRENT RATING : 1.5 A AT 20°C (FULLY LOADED)
1 A AT 70°C (FULLY LOADED)
RATED VOLTAGE : 500 V AC (CONT / CONT)
OPERATING TEMPERATURE : -55°C TO 125°C
CONTACT RESISTANCE : 20 mΩ MAX
INSERTION FORCE : 0.75 N MAX / CONT
EXTRACTION FORCE : 0.15 N MIN / CONT
INSULATION RESISTANCE : 10⁴ MΩ MIN

VISUAL POLARISATION AT COLUMN 25
SHOULD COINCIDE WITH 25TH COLUMN ON PCB

NOTE 1: "--" PERFORMANCE LEVEL INDICATION

GC: PL3
GF: PL2
GL: PL1

LAY-OUT
P.C.B.- HOLE
(FRONT SIDE)




THIS IS OUR EXCLUSIVE PROPERTY. IT IS NOT TO BE COPIED, REPRINTED
OR DISCLOSED TO A THIRD PARTY. NOR USED FOR MANUFACTURING WITHOUT
OUR WRITTEN CONSENT, AND HAS TO BE RETURNED TO US IN CASE OF NO USAGE

DIT IS ONZE EIGENDOM EN MAG NOCH NAGEMAAKT, HERDRUKT, OVERGEMAAKT AAN
DERDEN, NOCH VOOR FABRIKATIE GEBRUIKT WORDEN, ZONDER ONZE SCHRIFTELIJKE
TOELATING. BIJ NIET GEBRUIK IS TERUGZENDING VERPLICHT.

FEMALE SIGNAL STRAIGHT PRESS-FIT -TO-BOARD CONNECTOR

WITHOUT SERVICECENTER

1DEC ±0,2 1DEC 2DEC ±0,1 2DEC ANGLES ±1° HOEKEN	APPR.	DATE	SIGN.	MPACS 5R STR REC CONN TYPE B		
WE RESERVE THE RIGHT TO CHANGE DIMENSIONS OR REQUIREMENTS WITHOUT PRIOR NOTICE.	DRAFT	10.04.98	M.Fret	CAT. No. HM2S02PK5100--		
	CHECKED			A FCI FCI MECHELEN N.V. A. SPINOYSTRAAT 8, 2800 MECHELEN		SCALE
	PROD. MGR.					3 / 1
ALL DIMENSIONS IN MM	PR.ENG. MGR.			BS,C ,201907,012		C
	PR.MGT. MGR.					
	REFERENCES / REFERENTIES					
ALLE AFMETINGEN IN MM						