

TLS 2200®/TLS PC Link™ Labels



TLS 2200®/TLS PC Link™ Label Index By Size (Continued)

Diagram	Catalog Number	Labels Per Roll	Material	Color	B-Number	Label Width Inch (mm) A	Label Height Inch (mm) B	Write-On Height Inch (mm) C	Wire Gauge
1.000" (Continued)									
Fig. 7	PTL-19-427	250	Vinyl	White	B-427	1.000 (25.4)	1.000 (25.4)	0.375 (9.5)	12 to 10
Fig. 7	BPTL-19-427	2500	Vinyl	White	B-427	1.000 (25.4)	1.000 (25.4)	0.375 (9.5)	12 to 10
Fig. 7	PTL-19-427-BL	250	Vinyl	Blue	B-427	1.000 (25.4)	1.000 (25.4)	0.375 (9.5)	12 to 10
Fig. 7	PTL-19-427-BR	250	Vinyl	Brown	B-427	1.000 (25.4)	1.000 (25.4)	0.375 (9.5)	12 to 10
Fig. 7	PTL-19-427-GR	250	Vinyl	Green	B-427	1.000 (25.4)	1.000 (25.4)	0.375 (9.5)	12 to 10
Fig. 7	PTL-19-427-GY	250	Vinyl	Gray	B-427	1.000 (25.4)	1.000 (25.4)	0.375 (9.5)	12 to 10
Fig. 7	PTL-19-427-OR	250	Vinyl	Orange	B-427	1.000 (25.4)	1.000 (25.4)	0.375 (9.5)	12 to 10
Fig. 7	PTL-19-427-PL	250	Vinyl	Purple	B-427	1.000 (25.4)	1.000 (25.4)	0.375 (9.5)	12 to 10
Fig. 7	PTL-19-427-RD	250	Vinyl	Red	B-427	1.000 (25.4)	1.000 (25.4)	0.375 (9.5)	12 to 10
Fig. 7	PTL-19-427-YL	250	Vinyl	Yellow	B-427	1.000 (25.4)	1.000 (25.4)	0.375 (9.5)	12 to 10
Fig. 7	PTL-19-642	250	Vinyl	White	B-427	1.000 (25.4)	1.000 (25.4)	0.375 (9.5)	12 to 10
Fig. 4	PTL-19-435	250	Polyester	Silver	B-435	1.000 (25.4)	1.000 (25.4)	—	—
Fig. 4	PTL-19-483	250	Polyester	White	B-483	1.000 (25.4)	1.000 (25.4)	—	—
Fig. 4	PTL-19-486	250	Polyester	Silver	B-486	1.000 (25.4)	1.000 (25.4)	—	—
Fig. 4	PTL-19-489	250	Polyester	White	B-489	1.000 (25.4)	1.000 (25.4)	—	—
Fig. 4	PTL-19-422	250	Polyester	White	B-422	1.000 (25.4)	1.000 (25.4)	—	—
Fig. 4	PTL-19-423	250	Polyester	White	B-423	1.000 (25.4)	1.000 (25.4)	—	—
Fig. 4	BPTL-19-423	2500	Polyester	White	B-423	1.000 (25.4)	1.000 (25.4)	—	—
Fig. 7	PTL-19-427	250	Vinyl	White	B-427	1.000 (25.4)	1.000 (25.4)	0.375 (9.5)	—
Fig. 7	BPTL-19-427	2500	Vinyl	White	B-427	1.000 (25.4)	1.000 (25.4)	0.375 (9.5)	—
Fig. 7	PTL-19-427-BL	250	Vinyl	Blue	B-427	1.000 (25.4)	1.000 (25.4)	0.375 (9.5)	—
Fig. 7	PTL-19-427-BR	250	Vinyl	Brown	B-427	1.000 (25.4)	1.000 (25.4)	0.375 (9.5)	—
Fig. 7	PTL-19-427-GR	250	Vinyl	Green	B-427	1.000 (25.4)	1.000 (25.4)	0.375 (9.5)	—
Fig. 7	PTL-19-427-GY	250	Vinyl	Gray	B-427	1.000 (25.4)	1.000 (25.4)	0.375 (9.5)	—
Fig. 7	PTL-19-427-OR	250	Vinyl	Orange	B-427	1.000 (25.4)	1.000 (25.4)	0.375 (9.5)	—
Fig. 7	PTL-19-427-PL	250	Vinyl	Purple	B-427	1.000 (25.4)	1.000 (25.4)	0.375 (9.5)	—
Fig. 7	PTL-19-427-RD	250	Vinyl	Red	B-427	1.000 (25.4)	1.000 (25.4)	0.375 (9.5)	—
Fig. 7	PTL-19-427-YL	250	Vinyl	Yellow	B-427	1.000 (25.4)	1.000 (25.4)	0.375 (9.5)	—
Fig. 7	PTL-103-427	250	Vinyl	White	B-427	1.000 (25.4)	1.250 (31.8)	0.500 (12.7)	10 to 4
Fig. 6	PTL-31-499	250	Nylon	White	B-499	1.000 (25.4)	1.500 (38.1)	—	10 to 4
Fig. 6	PTL-31-498	250	Vinyl	White	B-498	1.000 (25.4)	1.500 (38.1)	—	10 to 4
Fig. 7	PTL-31-427	250	Vinyl	White	B-427	1.000 (25.4)	1.500 (38.1)	0.500 (12.7)	10 to 4
Fig. 7	BPTL-31-427	2500	Vinyl	White	B-427	1.000 (25.4)	1.500 (38.1)	0.500 (12.7)	10 to 4
Fig. 7	PTL-31-427-BL	250	Vinyl	Blue	B-427	1.000 (25.4)	1.500 (38.1)	0.500 (12.7)	10 to 4
Fig. 7	PTL-31-427-BR	250	Vinyl	Brown	B-427	1.000 (25.4)	1.500 (38.1)	0.500 (12.7)	10 to 4
Fig. 7	PTL-31-427-GR	250	Vinyl	Green	B-427	1.000 (25.4)	1.500 (38.1)	0.500 (12.7)	10 to 4
Fig. 7	PTL-31-427-GY	250	Vinyl	Gray	B-427	1.000 (25.4)	1.500 (38.1)	0.500 (12.7)	10 to 4

