


T-Series



The T-Series Mini Tippette snap-in rocker switches are single pole with ratings up to 20 amps. A variety of circuits, actuators and terminations are available.

- Specifications
- Certifications*: UL, CSA, VDE
 - Dielectric Strength: 1,000 V (minimum)
 - Insulation Resistance: 100 Megohms (minimum)
 - Base Material: Nylon
 - Actuator Material: Nylon
 - Bezel Material: Nylon

* Due to ongoing technological advances, consult factory for certification specifics.



SERIES

T

SINGLE POLE

CIRCUIT

A ON-NONE-OFF
B ON-NONE-ON
C ON-OFF-ON

RATING¹

10 5A 250VAC
10A 125VAC
1/2HP 125-250VAC
11 5A 250VAC
10A 125VAC
5A (TUNGSTEN)
125VAC L
20 10A 250VAC
15A 125VAC
3/4HP 125-250VAC
22 10A 250VAC
15A 125VAC
20A 125-250VAC H
3/4HP 125-250VAC
25 10A 250VAC
16A 125VAC
1/2HP 125-250VAC

TERMINATION/FUNCTION

FUNCTION	SOLDER LUG	.250 TAB (QC)	.187 TAB (QC)	WIRE LEAD
ON-NONE-OFF	0	1	3	5
(ON)-NONE-OFF	A	B	D	F
ON-NONE-(OFF)	L	M	R	T
ON-NONE-ON	0	1	3	5
ON-NONE-(ON)	A	B	D	F
ON-OFF-ON	0	1	3	5

ACTUATOR STYLE²

P PADDLE
PL PLUNGER
PS PADDLE - SHORT
T ROCKER
TL MOMENTARY ROCKER

ACTUATOR COLOR³

B BLACK
W WHITE

BASE COLOR³

B BLACK
W WHITE

NOTES:
Shading indicates standard configurations. Stainless steel bezels are available. Add suffix "Bezel" to the end of the catalog number. (ex.) TA201-TB-B/BEZEL
Imprinting is available. Please specify when ordering. (ex. TA201-TB-B/ON-OFF)
Panel Cut-Out Recommendations: For sheet metal panels, switch must enter panel in same direction as the punch. (Burr on bottom.) Test cut hole in actual material.
1 Rating Code 22 is 20A 125VAC inductive when momentary function is specified. Rating Code 22 only available with circuits A & B. Rating Code 25 only available with PL-Plunger actuator.
2 PL-Plunger actuator available only in T Series with circuit A, termination/function B or F, and terminals at T1 and 2.
3 Custom colors are available. Consult factory.