

4" SPEAKER



No. TS40

Fine quality replacement speaker. 4" speaker with 1.7 oz. ceramic magnet. Speaker is 8 ohm impedance rated at 5 watts.

5" SPEAKER



No. TS50

Fine quality replacement speaker. 5" speaker with 1.7 oz. ceramic magnet. Speaker is 4 ohm impedance rated 6 watts.

6" SPEAKER



No. TS60

Fine quality replacement speaker. 6" speaker with 3.0 oz. ceramic magnet. Speaker is 8 ohm impedance rated at 10 watts nominal 15 watts peak.

INDOOR/OUTDOOR TRUMPET SPEAKERS WITH PLENTY OF POWER TO SPARE



No. WP13 25 WATTS RMS

No. WP12 15 WATTS RMS

• ALL WEATHER • RUST RESISTANT • SHOCK RESISTANT • SWIVEL MOUNTING BRACKET • PAGING: SPORTING EVENTS • MARINE • AUDITORIUM

Hot or cold, the smooth response will hold because these reflex horn speakers can withstand extreme climatic conditions without any loss.

Lightweight heavily enameled ABS plastic has a rubber, sound-dampening ring around the outside edge and is attached to a 24" color-coded connecting cord, stripped and tinned.

SPECIFICATIONS:

Model No.	Horn Opening	Frequency Response	Impedance	Power Rating
WP12	5" x 8"	350-13,000 Hz	8 ohms	15 Watts
WP13	6" x 11"	300-12,000 Hz	8 ohms	25 Watts



No. WP7 5" REFLEX TRUMPET HORN

NEITHER SLEET,
NOR SNOW, NOR
RAIN STOPS
THIS TRUMPET
HORN SPEAKER

Construction is of ABS plastic and the driver is protected by a rubber seal for weather and weatherproofing. The efficient sound displacement is consistent, whether used indoors or out.

The beautiful, metallic blue horn is mounted on a stand, fully adjustable through 90°

Power Rating: 10 Watts (RMS) **Frequency Response:** 450-10,000 Hz **Impedance:** 8 Ohms **Cable:** 1 Ft. **Size:** 5" x 5" x 5" **Weight:** 1 Pound

8" SPEAKER

This quality 8" speaker is well-suited for public address systems and background music installations. Metal frame has mounting holes for line matching transformers.

Power rating: 20W; 10 oz. magnet; 1 "voice coil; 8-ohm impedance.

No. SP800

