


Digital Calipers

Roebuck



Calipers have hardened stainless steel frame and measuring jaws, depth rod, thumbroll adjustment and knurled locking screw. 3 button operation: On/Off: Inch/Metric conversion. Zero in any position.

Accuracy
±0.02mm < 100mm
±0.03mm > 100 - 200mm
±0.04mm > 200 - 300mm

489576

Capacity (mm)	Capacity (in)	Resolution	External Jaw	Internal Jaw	Order Code	Price Each
150	6	0.01mm/0.0005in	40mm	18mm	137-5863	
200	8	0.01mm/0.0005in	50mm	20mm	137-5864	
300	12	0.01mm/0.0005in	60mm	20mm	137-5865	