



CGS Computer Grade Capacitors

High performance computer grade capacitor. Long life expectancy available in high or low post configurations. **Operating Temperature:** -40°C to +85°C. Low ESR high ripple capabilities. **Voltage Range:** 6.3 WVDC 500 WVDC. **Tolerance:** -10% +75% up to 150 WVDC, -10% +50%, 200-450 WVDC.

Stock No.	Mfr.'s Type	WV DC	MFD	Case Size (In.) Dia. x L	EACH		
					1-24	25-49	50-99
857-0201	CGS133U010R2C	10	18000	13/8 x 21/8	9.60	8.78	8.08
857-0051	CGS133U016R2C	16	15000	13/8 x 31/8	9.63	8.74	7.99
857-0052	CGS133U016R3C	16	17000	13/8 x 31/8	9.75	8.81	7.36
857-0200	CGS243U016R3C	16	24000	19/8 x 31/8	9.14	8.24	7.64
857-0054	CGS253U016V2C	16	25000	2 x 21/8	11.50	9.32	8.66
857-0055	CGS253U016R4C	16	34000	19/8 x 41/8	12.11	10.39	10.5
857-0056	CGS253U016V3C	16	38000	2 x 31/8	12.45	11.42	10.44
857-0216	CGS563U016V3C	16	55000	2 x 31/8	14.20	13.02	11.90
857-0202	CGS563U016X3C	16	66000	2 x 41/8	18.09	16.32	14.86
857-0204	CGS140U016X5C	16	100000	3 x 51/8	33.97	30.64	28.41
857-0060	CGS140U016W4C	16	110000	21/2 x 41/8	23.53	21.58	19.91
857-0206	CGS124U016X3L	16	120000	3 x 31/8	29.11	26.28	24.35
857-0224	CGS214U016X5R	16	210000	3 x 51/8	38.94	35.70	32.95
857-0006	CGS562U025R3C	25	5600	19/8 x 31/8	9.33	8.46	7.73
857-0007	CGS589U025R3C	25	8900	19/8 x 31/8	11.00	9.98	9.12
857-0208	CGS130U025R3C	25	10000	19/8 x 31/8	3.29	7.48	6.94
857-0008	CGS123U025V3C	25	12000	2 x 31/8	11.67	10.59	9.69
857-0038	CGS183U025V4C	25	18000	19/8 x 41/8	13.02	11.82	10.80
857-0065	CGS283U025V3C	25	28000	2 x 31/8	14.20	13.02	11.89
857-0046	CGS293U025V4C	25	29000	2 x 41/8	18.16	16.65	15.22
857-0125	CGS473U025V4C	25	47000	2 x 41/8	16.82	15.42	14.09
857-0236	CGS633U025W4C	25	65000	21/2 x 41/8	22.98	21.07	19.25
857-0175	CGS124U025X4C	25	120000	3 x 41/8	34.64	31.76	23.27
857-0240	CGS452U030R2C	30	4500	19/8 x 21/8	8.05	7.26	6.73
857-0121	CGS802U030R3C	30	8000	19/8 x 31/8	6.90	8.09	7.39
857-0072	CGS303U030V4C	30	30000	2 x 41/8	15.74	14.43	13.18
857-0212	CGS553U030W4C	30	55000	21/2 x 41/8	24.44	22.04	20.44
857-0129	CGS104U030X5L	30	100000	3 x 51/8	39.72	36.77	33.95
857-0274	CGS123U035R4C	35	12000	19/8 x 41/8	10.11	9.19	8.40
857-0280	CGS730U035X4C	35	70000	3 x 41/8	34.38	31.52	29.09
857-0012	CGS222U040R2C	40	2200	19/8 x 21/8	7.82	7.09	6.49
857-0047	CGS272U040R2C	40	2700	19/8 x 21/8	7.76	7.04	6.44
857-0080	CGS352U040R2C	40	3500	19/8 x 21/8	7.97	7.22	6.60
857-0013	CGS422U040R3C	40	4200	19/8 x 31/8	9.50	8.62	7.88
857-0124	CGS472U040R2C	40	4700	19/8 x 21/8	11.88	10.79	9.85
857-0014	CGS512U040R3C	40	5100	19/8 x 31/8	8.19	7.43	6.80
857-0073	CGS602U040R3C	40	6000	19/8 x 31/8	9.31	8.45	7.72
857-0130	CGS902U040R4C	40	9000	19/8 x 41/8	10.26	9.31	8.51
857-0015	CGS113U040V3C	40	11000	2 x 31/8	12.11	10.99	10.05
857-0214	CGS123U040R4C	40	12000	19/8 x 41/8	10.31	9.30	8.62
857-0077	CGS133U040V4C	40	13000	2 x 41/8	14.30	12.63	11.57
857-0016	CGS173U040V4C	40	17000	2 x 41/8	13.77	12.62	11.54
857-0009	CGS173U040V3C	40	17000	2 x 31/8	14.95	13.58	10.56
857-0218	CGS203U040V5L	40	20000	2 x 51/8	18.94	17.08	15.84
857-0131	CGS222U040V3C	40	22000	2 x 31/8	19.25	17.65	16.14
857-0220	CGS233U040V4C	40	23000	2 x 41/8	14.79	13.34	12.37
857-0179	CGS333U040V4C	40	33000	2 x 41/8	21.47	20.02	18.17
857-0036	CGS403U040W4C	40	40000	21/2 x 41/8	22.84	20.93	19.13
857-0222	CGS683U040X4C	40	68000	3 x 41/8	35.99	32.46	30.10
857-0081	CGS162U050R2C	50	1600	19/8 x 21/8	7.75	7.05	6.43
857-0017	CGS222U050R2C	50	2200	19/8 x 21/8	7.57	6.86	6.28
857-0083	CGS292U050R3C	50	2900	19/8 x 31/8	9.06	8.22	7.52
857-0018	CGS412U050R3C	50	4100	19/8 x 31/8	9.34	8.48	7.75
857-0084	CGS492U050R3L	50	4900	19/8 x 31/8	10.18	9.24	8.44
857-0134	CGS562U050R3C	50	5000	19/8 x 31/8	9.72	8.83	8.07
857-0228	CGS612U050R4C	50	6100	19/8 x 41/8	9.80	8.84	8.20
857-0086	CGS663U050V3C	50	6500	2 x 31/8	11.55	10.48	9.56
857-0284	CGS682U050R3C	50	6800	19/8 x 31/8	10.25	9.31	8.51
857-0021	CGS962U050V4C	50	9600	2 x 41/8	19.56	17.93	16.38
857-0136	CGS103U050R4C	50	10000	19/8 x 41/8	11.51	10.46	9.53
857-0137	CGS133U050V3C	50	13000	2 x 31/8	14.41	13.21	12.06
857-0088	CGS153U050V4C	50	15000	2 x 41/8	14.71	13.47	12.32
857-0499	CGS183U050V3C	50	18000	2 x 31/8	16.68	14.74	13.46
857-0139	CGS203U050V4C	50	20000	2 x 41/8	17.01	15.60	14.26
857-0040	CGS242U050W3C	50	24000	21/2 x 31/8	30.41	27.88	25.74
857-0140	CGS253U050W4C	50	25000	21/2 x 41/8	21.43	19.65	17.96
857-0044	CGS273U050V4C	50	27000	2 x 41/8	22.73	20.83	19.03

Computer Grade Capacitors

Stock No.	Mfr.'s Type	WV DC	MFD	Case Size (In.) Dia. x L	EACH		
					1-24	25-49	50-99
857-0230	CGS133U050W4C	50	31000	21/2 x 41/8	25.06	23.60	20.96
857-0232	CGS433U050X5						