


NOTES: UNLESS OTHERWISE SPECIFIED

1. CONSTRUCTION:
INSULATOR: P.V.C. AVAILABLE IN BLACK OR RED.
CONTACT: ANACONDA 7021 OR BOILCAT C97.
GOLD PLATED.

SOCKET: BRASS. TIN PLATED.

2. PERFORMANCE:
MAXIMUM CURRENT: 4 AMPS
MAXIMUM VOLTAGE: 300 V
MAXIMUM TEMPERATURE: 122°F (50°C)



		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: FRACTIONS DECIMALS ANGLES		CONTRACT NO.		DESCRIPTION	
		± .XX ± .XXX ± ±		APPROVALS	DATE	E-Z-HOOK DIVISION OF TEKTEST INC. ARCADIA, CA 91006 U.S.A.	
				DRAWN	R.L.		
				APPROVED BY	1/11		
		MATERIAL SEE NOTE.				E-Z-FLEX BAN SKT TO 0.030 [0.76] PIN ADAPTER (22AWG)	
		FINISH SEE NOTE.					
		NEXT ASSY USED ON					
		APPLICATION		DO NOT SCALE DRAWING		SIZE	CODE IDENT NO. DRAWING NO.
						A	08505 9338
						SCALE	2:1
						SHEET 1 OF 1	