

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0712201400](#)
Status: **Obsolete**
Description: 1.00mm (.039") Pitch SMT, Right Angle, ZIF, Top Contact Style Receptacle, 1.00mm (.039") PC Tail Length, with LCP Actuator, 14 Circuits
Replacement Part Number: 52207 SERIES

Documents:
[Drawing \(PDF\)](#)

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	FFC/FPC Connectors
Series	71220
Product Name	N/A
Replacement Part Number	52207 SERIES

Physical

Circuits (Loaded)	14
Color - Resin	Black, Natural
Contact Position	Top
Entry Angle	90° Angle
Flammability	94V-0
Mated Height	2.70mm (.106")
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin-Lead
Material - Plating Termination	Tin-Lead
Material - Resin	High Temperature Thermoplastic
Number of Rows	1
Orientation	Right Angle
PCB Locator	No
PCB Retention	None
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	1.00mm (.039")
Plating min - Mating	5.080µm (200µ")
Plating min - Termination	5.080µm (200µ")
Polarized to PCB	No
Stackable	No
Surface Mount Compatible (SMC)	N/A
Temperature Range - Operating	-20°C to +80°C
Termination Interface: Style	Surface Mount
Wire/Cable Type	FFC/FPC

Electrical

Current - Maximum per Contact	0.5A, 1A
Voltage - Maximum	125V

Material Info

Old Part Number	A712201400
-----------------	------------

EU RoHS
Not RoHS Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[71220Series](#)