


Number of contacts

6-64



Male header with straight solder pins

| Identification                                          | No. of contacts | Part No.       |        |                   |        |                  |        |
|---------------------------------------------------------|-----------------|----------------|--------|-------------------|--------|------------------|--------|
|                                                         |                 | Without levers |        | With short levers |        | With long levers |        |
| Male header with straight solder pins<br>Length: 2.9 mm | 6               | 09 18 506      | └ 924  | 09 18 506         | └ 914  | 09 18 506        | └ 904  |
|                                                         | 10              | 09 18 510      | └ 924  | 09 18 510         | └ 914  | 09 18 510        | └ 904  |
|                                                         | 14              | 09 18 514      | └ 924  | 09 18 514         | └ 914  | 09 18 514        | └ 904  |
|                                                         | 16              | 09 18 516      | └ 924  | 09 18 516         | └ 914  | 09 18 516        | └ 904  |
|                                                         | 20              | 09 18 520      | └ 924  | 09 18 520         | └ 914  | 09 18 520        | └ 904  |
|                                                         | 24              | 09 18 524      | └ 924  | 09 18 524         | └ 914  | 09 18 524        | └ 904  |
|                                                         | 26              | 09 18 526      | └ 924  | 09 18 526         | └ 914  | 09 18 526        | └ 904  |
|                                                         | 30              | 09 18 530      | └ 924  | 09 18 530         | └ 914  | 09 18 530        | └ 904  |
|                                                         | 34              | 09 18 534      | └ 924  | 09 18 534         | └ 914  | 09 18 534        | └ 904  |
|                                                         | 40              | 09 18 540      | └ 924  | 09 18 540         | └ 914  | 09 18 540        | └ 904  |
|                                                         | 50              | 09 18 550      | └ 924  | 09 18 550         | └ 914  | 09 18 550        | └ 904  |
|                                                         | 60              | 09 18 560      | └ 924  | 09 18 560         | └ 914  | 09 18 560        | └ 904  |
|                                                         | 64              | 09 18 564      | └ 924  | 09 18 564         | └ 914  | 09 18 564        | └ 904  |
| Male header with straight solder pins<br>Length: 4.5 mm | 6               | 09 18 506      | └ 922* | 09 18 506         | └ 912* | 09 18 506        | └ 902* |
|                                                         | 10              | 09 18 510      | └ 922* | 09 18 510         | └ 912* | 09 18 510        | └ 902* |
|                                                         | 14              | 09 18 514      | └ 922* | 09 18 514         | └ 912* | 09 18 514        | └ 902* |
|                                                         | 16              | 09 18 516      | └ 922* | 09 18 516         | └ 912* | 09 18 516        | └ 902* |
|                                                         | 20              | 09 18 520      | └ 922* | 09 18 520         | └ 912* | 09 18 520        | └ 902* |
|                                                         | 24              | 09 18 524      | └ 922* | 09 18 524         | └ 912* | 09 18 524        | └ 902* |
|                                                         | 26              | 09 18 526      | └ 922* | 09 18 526         | └ 912* | 09 18 526        | └ 902* |
|                                                         | 30              | 09 18 530      | └ 922* | 09 18 530         | └ 912* | 09 18 530        | └ 902* |
|                                                         | 34              | 09 18 534      | └ 922* | 09 18 534         | └ 912* | 09 18 534        | └ 902* |
|                                                         | 40              | 09 18 540      | └ 922* | 09 18 540         | └ 912* | 09 18 540        | └ 902* |
|                                                         | 50              | 09 18 550      | └ 922* | 09 18 550         | └ 912* | 09 18 550        | └ 902* |
|                                                         | 60              | 09 18 560      | └ 922* | 09 18 560         | └ 912* | 09 18 560        | └ 902* |
|                                                         | 64              | 09 18 564      | └ 922* | 09 18 564         | └ 912* | 09 18 564        | └ 902* |
| Kinked version on request                               |                 |                |        |                   |        |                  |        |

\* Not normally kept in stock  
For accessories see page 08.18  
For dimensions see page 08.11

For performance level 3 please specify digit  
For performance level 2 please specify digit  
S4 = 0.76 µm (30 µinch) Au or PdNi equivalent

