

[Request more info](#)**Part Number : 5219270F**

5219270F



This is a
RoHS Compliant Product
[To learn more click here](#)

General Description

Series	521
Configuration	5 mm Lens
Description	Discrete LED Lamp
Package Options	Bulk Packaging
Sizes	5mm
Lamp Type	Single Color
Lens Color	Diffused

Absolute Maximum Ratings (Ta = 25°)

Forward Current mA	40mA
Reverse Current	10 @ Vr = 5V
Operating Temperature	-55~+100
Storage Temperature	-55~+100

Operating Characteristics

LED Type	GaP
Color	Green 
Luminous Intensity Min	4.5
Luminous Intensity Typical	5.8
Luminous Intensity Max	7.1
Test Current mA	10mA
Dominant Wavelength Typical	570nm
Power Dissipation Max	130mW

[Share](#) |

|