







TIN LEAD PART NUMBER						
SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER
09	30.81	24.99	16.96	16.79	10.96	D09P24A*GL00
15	39.14	33.32	25.18	25.12	19.18	D15P24A*GL00
25	53.03	47.04	39.12	38.84	33.12	D25P24A*GL00
37	69.32	63.50	55.68	55.30	49.68	D37P24A*GL00

Protection: 4	--> flash AU
6	--> 0.76μ AU



LEAD FREE PART NUMBER						6 -->
SHELL	A $\pm$ 0.38	B $\pm$ 0.12	C $\pm$ 0.10	D $\pm$ 0.25	E $\pm$ 0.07	PART NUMBER
09	30.81	24.99	16.96	16.79	10.96	D09P24A*GL00LF
15	39.14	33.32	25.18	25.12	19.18	D15P24A*GL00LF
25	53.03	47.04	39.12	38.84	33.12	D25P24A*GL00LF
37	69.32	63.50	55.68	55.30	49.68	D37P24A*GL00LF

Protection: 4 $\rightarrow$ flash AU
 6 $\rightarrow$ 0.76 μ AU

PC card drilling dimensions(after plating)
(thickness 1.60±0.20mm)



rev	ecn no	dr	date
C	-	JOU	1996/09/09
D	LS05-001	MPE	2005/03/09
E	LS05-0056	MPE	2005/06/27
F	LS06-0097	LGO	2006/07/29
G	IO9-0268	NG	2009-11-24
H	II0-0059	NG	2010-02-23
I	-	-	-

www.fciconnect.com		surface ISO 1302		✓	tolerance std ISO 406 ISO 1101		projection 	mm 
		TOLERANCES UNLESS OTHERWISE SPECIFIED						
Dr	JOUBERT	1994-09-23	ANGULAR		0.X	±0.1	size A3	Scale 2
Eng	PESSON	1994-09-23		LINEAR	0.XX	±0.1		
Chr	NIRMAL GEORGE	2010-02-23	0.XX	±2°			ECN	110-0059
Appr	SUDHIR VARMA	2010-02-23	Product family			D-SUB	Spec ref -	
		MALE CONNECTEUR DELTA D S				dwg no		Rev.
						C01-8646-0099		
title straight solder type for						CUSTOMER		sheet 1 of 1
catalog no		-						

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:

SEE DRAWING C01-8646-0000

European Views

Copyright FCI.

