



Representative

Catalog Number: 127
Product ID: 7TAD013470R0000
UPC Number: 78621000127
EAN Number: 05414363137207
Status: A

2 Inch Malleable Iron Bushing for Use with Rigid/IMC Conduit

- High ribs make tightening easy with fingers or with wrench.
- Locknut-type base gives improved bonding and resist loosening under conditions of vibration.

North American Specifications (UNSPSC)

UNSPSC	39121312 Electrical bushing
IGCC	4442 Electrical bushing
Brand Name	T&B
Type	Bushings
Special Features	Smoothly Rounded Shoulder Covers End of Conduit; Broad Flange Covers Knockout Hole.
Application	For Use with Rigid/IMC Conduit
Standard	UL E23018, CSA
Size	2 Inch
Material	Malleable Iron

European Specifications (ETIM)

ETIM	EC001181 Sealing ring
Model	Other
Outer diameter	67.468mm
Material	Metal
Fitting for thread size NPT	2.00

Packaging

Inner Quantity	25
Inner Dimensions (inches)	8.2x4.19x5.7
Outer Quantity	50
Outer Dimensions (inches)	8.6x5.6x8.8
Weight Uom	18.5 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-000019
Technical Drawing / Data Sheet Canada	Available on Website

Header

3D Model	Available on Website
----------	----------------------

For further technical assistance, please contact us...

ABB Installation Products - USA
860 Ridge Lake Blvd.
Memphis, TN 38120
www.tnb.com

ABB Installation Products Technical Support
MS 3B-50
860 Ridge Lake Blvd.
Memphis, TN 38120

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com