



GREENLEE®
A Textron Company

MADE FOR THE TRADE!™

WIRE FERL UNINSUL

Non-Insulated Wire Ferrules



Image
Unavailable

Cat No: 75/25VZ

UPC No: 783310050261

Description

- For terminating stranded wire into terminal blocks
- Electrolytic copper and tin plating provide maximum conductivity and low contact resistance
- Meets DIN 46228, part 1, 0.5 - 50 mm²

Specifications

- Finish : Tin Plated
- Material : Electrolytic Copper
- Recommended Crimping Tools : K32GL, K34GL, K36GL, K30GL, Die 03283
- Size : 0.984 IN (25.000 MM) Overall Length
- Type : Non Insulated
- Wire Size : 10 AWG (6.000 SQ-MM)
- Wire Type : Stranded