

MINI FEED-THROUGH


Panel Mount

For use when space constraints require extremely compact solutions and internal jumping is required.


Individual components can be used to build your own assemblies. Just snap the required number of terminal block components together and place a Mounting Section on each end.

The CMB 4 accepts internal jumpers and standard marking tags.

- Extremely compact and cost effective
- High density
- Screw-cage clamp
- Internal jumping provision
- Polyamide 6.6
- Standard color: gray




CMB4




EP CMB4

Preassembled blocks are also available for quick and easy installations.
See Dimensions below.




Dimensions mm (in.)
CMB4

Terminal Width	6 mm
Height x Length	28 x 27 mm
Stripping Length	9 mm
Insulation Material	Polyamide 6.6
Type of Connection	2 screw clamps & 1 tapped hole for cross connection
Approvals	
Wire Range	22-10 AWG 0.5-4 sq.mm 22-10 AWG
Voltage Rating	300 V 400 V 300 V
Current Rating	35 A 32 A 35 A
Torque	7 lb-in 0.5 Nm 7 lb-in

		Cat. No.	Std. Pk.
Terminal Block		CMB4	100
Mounting Section		EPCMB4	50
Separator Plate		SPCMB4	100
Mounting Screw*			
Internal Jumper		2 pole 3 pole 4 pole 10 pole	CA727/2 100 CA727/3 50 CA727/4 50 CA727/10 10
Insulated Internal Jumper		2 pole 3 pole 4 pole 10 pole	CA747/2 100 CA747/3 50 CA747/4 50 CA747/10 10
Current Bars		2 pole 3 pole 4 pole 10 pole 10 pole (breakable) 100 pole	CA703/1 100 CA704/1 100 CA705/1 100 CA732/10 100 CA732/10-A 100 CA732/100 10
Shorting Sleeve & Screw		CA607/S/Q	100
External Jumper		2 pole 3 pole 4 pole 10 pole	CA714/2 100 CA714/3 100 CA714/4 50 CA714/10 25
Marking Tags (MT Type)		MT2	100

Cat No.	No. of Poles	Width (a)	Hole Spacing (b)
CMB4/2	2	26 (1.02)	19 (0.75)
CMB4/3	3	32 (1.26)	25 (0.98)
CMB4/4	4	38 (1.50)	31 (1.22)
CMB4/5	5	44 (1.73)	37 (1.46)
CMB4/6	6	50 (1.97)	43 (1.69)
CMB4/7	7	56 (2.20)	49 (1.93)
CMB4/8	8	62 (2.44)	55 (2.17)
CMB4/9	9	68 (2.68)	61 (2.40)
CMB4/10	10	74 (2.91)	67 (2.64)
CMB4/11	11	80 (3.15)	73 (2.87)
CMB4/12	12	86 (3.39)	79 (3.11)
CMB4/13	13	92 (3.62)	85 (3.35)
CMB4/14	14	98 (3.86)	91 (3.58)
CMB4/15	15	104 (4.09)	97 (3.82)
CMB4/16	16	110 (4.33)	103 (4.06)
CMB4/17	17	116 (4.57)	109 (4.29)
CMB4/18	18	122 (4.80)	115 (4.53)
CMB4/19	19	128 (5.04)	121 (4.76)
CMB4/20	20	134 (5.28)	127 (5.00)
CMB4/21	21	140 (5.51)	133 (5.24)
CMB4/22	22	146 (5.75)	139 (5.47)
CMB4/23	23	152 (5.98)	145 (5.71)
CMB4/24	24	158 (6.22)	151 (5.94)



Mounting Section
EPCMB4

* Any length M3 screw may be used.