

PRODUCT NUMBER

73398-YXXXLF

RoHS COMPATIBLE, NOTE 6.

PACKAGING OPTIONS, NOTE 3.

PLATING

1= 0.76µm GOLD/GXT ON CONTACT AREA, 2µm TIN MIN ON TAILS

4= 2.0µm TIN MIN FULL PLATED

5= 0.25µm GOLD/GXT ON CONTACT AREA, 2µm TIN MIN ON TAILS

8= 0.38µm GOLD/GXT ON CONTACT AREA, 2µm TIN MIN ON TAILS

1.27µm NICKEL MIN UNDERLAYER FOR ALL PLATING VERSIONS

STYLE	SIZE	DIM "A"	OMIT PINS
01	2x05	5.84	A5
02	2x03	5.84	B2
03	2x04	5.84	B1
04	2x11	8.38	A6
05	2x20	8.38	B10
06	2x05	8.38	A5
07	2x08	5.84	B7
08	2x04	5.84	B4
09	2x20	5.84	A11
10	2x07	5.84	A4-B7
11	2x13	5.84	A3-B1
12	2x12	5.84	A2
13	2x05	5.84	B5
14	2x05	5.84	B4
15	2x03	5.84	A2-B2
16	2x03	16.40	A2
17	2x05	5.84	A4
18	2x05	5.84	A2,3,4 B2,3,4

NOTES:

1. HOUSING MAT'L : HIGH TEMPERATURE THERMOPLASTIC. UL94V-0 COLOR: BLACK

2. PIN MATERIAL : PHOSPHOR BRONZE

3 - PACKAGING OPTIONS:

= POLY BAGS

B = TUBE + CAP

A = TAPE & REEL WITH CAP, AS AVAILABLE

4. 9N MIN RETENTION IN EITHER DIRECTION

5. TO DETERMINE DIMENSIONS :

N = NUMBER OF POSITIONS PER ROW

EXAMPLE : 8 POS N x 2.54 = 20.32mm

6. RoHS COMPATIBLE PRODUCT SPECIFICATIONS

a - PLATING:

- "LF" MEANS THE PRODUCT IS LEAD-FREE, 2µm MINIMUM MATTE TIN OVER 1.27µm MINIMUM NICKEL UNDERPLATE.



b - MANUFACTURING PROCESS COMPATIBILITY

- THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 30 SECONDES IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN.



c - LABELING:

- MEETS PACKAGING SPECS AS PER GS-14-920

d - LEGAL STATEMENT: SEE GS-47-0004



OPTIONAL PICK-UP CAP
(SEE NOTE 3)



mat'l. code				surface	tolerance	projection	product family	
				ISO 1302	ISO 406 ISO 1101		HEADER	
ltr	ecn no	dr	date	tolerances unless otherwise specified			title	
R	B18983	LMU	14.10.03	angles	x.x ±0.3		HEADER DR,	
S	B-20597	AMA	15.03.30	linear	x.xx ±0.13		DUPLX SMT POLARIZED	
T	F-23055	AMA	16.01.15		x.xxx ±0.05		dwg no	
U	F-26753	DDE	17.04.20	dr	L.MULIN 99.04.12		sheet 1 of 1 size	
V	F-28256	LMU	17.10.25	enr	J. COMPAGNON 99.04.12		73398	
W	F-31154	DDE	18.09.04	chr			A3	
				appd	JMC		type CUSTOMER Drawing	
sheet index	revision							
	sheet							