




GUARDIAN
Electric Manufacturing

ISO 9001 / AS9100 Certified Company

Woodstock, IL 60098 Ph. (815)334-3600 Fax (815)337-0377

Or visit us at our website www.guardian-electric.com

Model TP8 x 16 Push-Type DC Tubular Solenoid



Solenoid shown energized and fully seated.

Supplied with mounting bracket, hex nut and lockwasher (not shown).

Spring kits are available (consult factory).

Total Weight: 5.80 oz.

Plunger Weight: 1.57 oz.

Model No.	Part No.	Duty Cycle	Voltage	Resistance (Ω)	Power (W)	Current
TP8x16-I-12	A420-066663-00	Intermittent	12VDC	9.3	16.3	1.29 A
TP8x16-C-12	A420-066662-00	Continuous	12VDC	28.3	5.3	424 mA
TP8x16-I-24	A420-066665-00	Intermittent	24VDC	36.1	16.8	665 mA
TP8x16-C-24	A420-066664-00	Continuous	24VDC	110	5.5	218 mA

When ordering, please refer to Part No., as listed above.

Consult factory for custom configurations.

Push Force (oz.)									Holding Force (oz.)
Stroke (in.)	0.050	0.125	0.250	0.375	0.500	0.625	0.750	1.000	-
Continuous Duty	24	14	9	4	3	2	1	N/A	83
Intermittent Duty	48	32	20	14	12	8	6	N/A	100

UL Recognition

Recognized under the 
Component Recognition Program of
Underwriters Laboratories, Inc.

Continuous Duty

100% 'On' Time

Intermittent Duty

25% 'On' Time, (100 Seconds 'On' Max.
Followed By 300 Seconds 'Off' Min.)

RoHS

These parts comply with **RoHS** Directive 2002/95/EC