


Home: Ring and Spade Terminals >

Part Number: 50225-7112

Ring Tongue Terminal for 14-16 AWG, Closed Un-insulated Brazed Barrel, Stud Size 6 (M3.5), Oxygen-Free Copper, Length 14.40mm



Series image - Reference only


Status:OBSOLETE


Replacement:Contact Molex


Series:50225

Category:Ring and Spade Terminals

Go to **Part Detail**▼

CHECK DISTRIBUTOR INVENTORY

Add to My Parts

Email this page

Product Environmental Compliance

[EU ELV](#):Product not active


[EU RoHS](#):Product not active


[EU RoHS Phthalates](#):Product not active


[China RoHS](#):

[REACH SVHC](#):Product not active

[Low-Halogen Status](#):Product not active

EU RoHS Certificate of Compliance (PDF)

Multiple Part Product Compliance Statements
EU RoHS, REACH SVHC, & Low-Halogen

Multiple Part Industry Compliance Documents

*IPC 1752A Class C
*IPC 1752A Class D
*Molex Product Compliance Declaration

Questions on Product Environmental Compliance? EmailProductCompliance@molex.com

Request Molex's CMRT from conflictminerals@molex.com

Application Tooling

FAQ

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Japan

Description	Product #
Hand Crimper For JIS Terminal	57257-5000
Hand Crimper For JIS Terminal	57343-5002

Crimp Quality Equipment

Molex also offers [wire strippers, pull testers, shut-height gauges, micro-meters and more](#)

Previously Available Application Tooling

[Check our list of old tooling that used to be available for this part](#)

Part Detail

COLLAPSE ALL

▼ General

Status	Obsolete
Category	Ring and Spade Terminals
Series	50225
Mil-Spec	N/A
Product Name	R (Ring)
Type	Ring
UPC	800753349049

▼ Physical

Barrel Type	Closed - Brazed
Insulation	None
Material - Plating Mating	Tin
Net Weight	610.000/mg
Packaging Type	Bag
Plating min - Mating	1.016µm
Plating min - Termination	1.016µm
Stud Size	6 (M3.5)
Termination Interface: Style	Crimp or Compression
Wire Size AWG	14, 16
Wire Size mm²	1.04-2.63

▼ Agency Certification

Please find UL Certificates by searching the UL Database using the Molex Series Number. [Click here to visit the UL Database](#)

UL	E134962
----	---------