

CARDMASTER PC 21/18-FC3



Order symbol:	PC 21/18-FC3
Product nbr:	7520281
Description:	Enclosure, PC
Remarks:	Grey screw cover

EAN: 6418074010261
El. number:
 Finland: 3438226
 :
 Norway:

Including: Base, terminal compartment cover with EPDM gasket and screws for mounting plate/DIN-rail. -3 and -L3 versions: Transparent cover with PUR gasket, hinges, locking devices; FC version: Closed PC frame front plate with PUR gasket and cover screws.

Sample photo

Dimensions:		Length	Width	Height	Rating:
mm:		213	185	102	Ingress Protection (EN 60529): IP 65
inch:		8.4	7.3	4.0	Impact Resistance (EN 62262): IK 08/07
Materials:					Electrical insulation: Totally insulated
Material:		Polycarbonate			Halogen free (DIN/VDE 0472, Part 815): Yes
Base colour:		RAL 7035			UV resistance: UL 508
Gasket material:		EPDM and Polyurethane			Flammability Rating (UL 746 C 5): UL 746C 5V
Temperatures:					Glow Wire Test (IEC 695-2-1) °C: 960
Short term:		-40 ... 120 °C			NEMA Class: NEMA 1, 3, 3R, 4X, 12, 13
Continuous:		-40 ... 80 °C			Certificates:
Short term:		-40 ... 250 °F			Underwriters Laboratories
Continuous:		-40 ... 175 °F			Fimko
Accessories:					Europe EN 62208: 2003
MP 21/18		Mounting plate			UL Canada
FP 21/18		Front plate (aluminium)			Gost R
FC PC 21/18		Frame of PC front plate			

CARDMASTER 213x185x90-119

