

REFERENCE SPECIFICATIONS

-NFC 93425 (in compliance with HE 507)

PHYSICAL CHARACTERISTICS

-INSULATOR MATERIAL: THERMOPLASTIC UL94V0

-CONTACT MATERIAL: BRASS

GOLD OVER NICKEL

-ACCESSORIES: STAINLESS STEEL or BRASS

Cadmium plated, yellow passivation

-SHELLS: STEEL

Cadmium plated, yellow passivation

ELECTRICAL CHARACTERISTICS

-NOMINAL CURRENT: 7.5A (SIGNAL CONTACT)

-CONTACT RESISTANCE: <=7.3 m Ohms SIGNAL

-CONTACT/CONTACT : >=1000 V

-CONTACT/GROUND : >=1200 V

-INSULATION RESISTANCE: >=5000 MOhms

- CLIMATIC CATEGORY: 55/125/21

TEMPERATURE RANGE -55°C TO +125°C

DAMP HEAT STEADY STATE 56 DAYS

SALT SPRAY 48 HOURS

Series

DBML13W3P300N

Shell size: **E A B C D**
see sheet 3

M :characteristic
for the DM series

Front accessory definition
see sheet 2

Blank :without accessory

L :threaded insert M3

O :threaded insert UNC 4-40

V :female screw UNC 4-40

F :floating mounting

S :spacer

Layout of contacts (see sheet 3)

Contacts

P :Pin

Termination type


3 Straight version

Plating

00 straight solder 500 matings/unmatings

43 straight solder 500 matings/unmatings for harsh environment

N :obligatory indication for HE 507 series





13W3 FOR EXAMPLE


www.fciconnect.com				surface ☒ tolerance std ISO 1302 ISO 406 ISO 1101		projection 		mm 							
				TOLERANCES UNLESS OTHERWISE SPECIFIED											
rev	ecn no	dr	date	Dr	M PESSON	2006/11/15	ANGULAR	0.X	±0.3	size	A2	Scale	2:1		
A	LS06-0174	MPE	2006/11/15	Eng	P LEGARE	2006/11/15	LINEAR	0.XX	±0.1						
B	LS07-0273	MPE	2007/10/30	Chr	P LEGARE	2006/11/15	0° ±2°	0.XXX	±0.05	ECN	LS07-0273				
-	-	-	-	Appr	P LEGARE	2006/11/15	Product family	-	-	Spec ref					
						SUB MALE DMW			deg no		C01-8637-1752			Rev	B
						mixed power straight solder									
						catalog no			-		CUSTOMER			sheet 1 of 7	
									-						




Copyright FCI.

















LAYOUT AND CONNECTOR DIMENSIONS




Floating signal contacts

REV F - 2006-08-17

LAYOUT AND CONNECTOR DIMENSIONS



SIDE VIEW FOR
LAYOUT: D



www.fciconnect.com			surface - ☒ tolerance std ISO 1302 ISO 406 ISO 1101		projection 		mm 	
			TOLERANCES UNLESS OTHERWISE SPECIFIED					
Dr	M PESSON	2006/11/15	ANGULAR	LINEAR	0.X	±0.3	size	Scale
Eng	P LEGARE	2006/11/15			0.XX	±0.1	A2	2:1
Chr	P LEGARE	2006/11/15	0° ±2°		0.XXX	±0.05	ECN	LS07-0273
Appr	P LEGARE	2006/11/15	Product family			- Spec ref		
			TITLE SUB MALE DMW mixed power straight solder			DWG NO C01-8637-1752		REV B
CATALOG NO -			CUSTOMER			SHEET 6 of 7		

