

Ladder Ties

PRO-POWER
Quality Cables



Stainless steel 316 cable ties, supplied either coated or uncoated. The coated cable ties have an electrostatically applied black epoxy finish, making them extremely resistant to corrosion. The construction of these ties gives them greater flexibility than the standard type.

- Self-locking for easy application
- Supplied in packs of 100

Operating temperature -80°C to +538°C Uncoated

Operating temperature -80°C to +150°C Coated

		Min. Tensile	Max.	Uncoated	Coated
Length	Width	Strength (kg)	Bundle Dia.	Order Code	Order Code
100	7	44.5		981-3675	981-3829
200	7	44.5	50	981-3683	981-3837
225	7	44.5	60	981-3691	981-3845
300	7	44.5	80	981-3705	981-3853
360	7	44.5	105	981-3713	981-3861
450	7	44.5	115	981-3721	981-3870
610	7	44.5	150	981-3730	981-3888
750	7	44.5	200	981-3748	981-3896
150	12	113.6		981-3756	981-3900
225	12	113.6	60	981-3764	981-3918
300	12	113.6	80	981-3772	981-3926
360	12	113.6	105	981-3780	981-3934
450	12	113.6	115	981-3799	981-3942
610	12	113.6	150	981-3802	981-3950
750	12	113.6	200	981-3810	981-3969

100 Per Pack