


1. SUGGESTED MOUNTING HOLE = $\varnothing.218$
2. HARDWARE IS INCLUDED.
3. MAX REFLOW IS 245°C FOR 5 SECONDS.
4. THIS IS A LEAD FREE PRODUCT.



LEAD FINISH: TIN/SILVER	
BUSHING FINISH: SILVER	
CAPACITANCE	.3uF +100/-0%
TEMP. RANGE	-55°C TO 125°C
CURRENT	10 AMP MAX.
WORKING VOLTAGE	85°C 80VDC MAX. 125°C 50VDC MAX.
D.C. RESISTANCE	.01ohms MAX.
MIN. I.L. PER MIL-STD-220 AT 25°C NO LOAD	
FREQ. MHZ	I.L. (db)
50 KHz	8
100KHz	13
1	32
10	47
100	60
500	70
1 GHz	70

BAG:
54F-786-013
DATE CODE
QTY./BAG (200 MAX.)

								01	00	REV. NO.	TOLERANCES UNLESS OTHERWISE SPECIFIED	api FAIRVIEW PENNSYLVANIA		
								CN #13142	CN 30519-CPD	CHANGE NOTICE	Fractions ± 1/64		Dwn.KAUFFMAN	Description FEED THRU
											Dec. .xx±	Dec. .xxx±.015	DATE 5-18-15	RESIN SEAL FILTER
											Angles ±0° 30'	CODE IDENT. NO. DLSP2	ENGR. ZAPATA	54F-786-013
												DO NOT SCALE		