

UNITEST *Ohmtest* Continuity Tester

Key Functions

- Acoustic continuity tester
- Optical continuity indication
- External voltage indication >50 V

General Information

- Areas of application: resistor, semiconductor, polarity, glow lamps, fuses etc.

Special Features

- Overload protected up to 600 V

Technical Data

Continuity Test	0...500 k Ω
Test Current	approx. 5 μ A
Test Voltage	< 9 V
External Voltage	
Indication	50...600 V
Protection Degree	IP 40
Safety complying with	IEC 61010, EN 61010
Power Supply	1 x 9 V / IEC 6LR61
Dimensions	210 x 58 x 24 mm
Weight	approx. 150 g



Scope of Supply:

- 1 pc UNITEST *Ohmtest*
- 1 pc Battery 9 V, IEC 6F22
- 1 pc Crocodile Clamp
- 2 pc Test Probes
- 1 pc Instruction Manual



Accessories:

Carrying Case
Cat. No. 1150

Order Information:

Description	Cat. No.
UNITEST <i>Ohmtest</i>	9072
Carrying Case	1150