



NO MERCURY ADDED


Description	: Mercury Free Extra Heavy Duty Battery, AAA Size
Chemical System	: Zinc Chloride
Nominal Voltage	: 1.5 Volts
Nominal Dimensions	: Ø10.5 mm x 44.5 mm
Terminals	: Protruded positive(+) and flat negative(-) contacts
Jacket	: Printed PVC shrink sleeve
Applications	: All electronic devices, e.g. toys, photographic equipment, data banks, calculators, audio appliances, remote controls, paging machines.
Warranty Period	: 36 months
Average Weight	: 9g

Cross References:



GP	JIS	IEC	Eveready
24G	R03	R03	1212

Typical Service Life:

Discharge Resistance	Discharge Condition	End Point Voltage	Service Life
15 Ohms	24 Hrs/ Day	0.9V	275 Mins



Model No.: **GP24G**



Unit : mm