

VECTORBORD® CIRCBORD™Part No. : 8021

Description :

3U x 160 mm, Hole Dia.: 0.025" , Grid: 0.05" x 0.05"

3U x 160mm Eurocard size

Copper plated-thru holes with solder plating


Peripheral ground plane

Low cost Vectorbord ® model for universal use

Constructed of 1/16" (0.062") FR-4

0.025" Dia. Holes

0.05" x 0.05" Grid



Circuit Pattern :

Peripheral Ground Plane, 0.05" Grid Pattern

Contacts :

N/A

Hole Diameter :

0.025" Dia. Copper Plated Thru holes with annular ring around each hole

Grid :

0.05" x 0.05"

Dimension { H, W, T } :

3U x 160 mm x 1.575 mm { 3.94" x 6.30" x 0.062" }

Material :

FR4 Epoxy Glass { MIL - P13949 type Gf }

Solder Terminals :

0.025" Dia. K36

NEMA Grade :

FR4

UL Flammability Class :

94V - 0