

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0982660350](#)
Status: **Active**
Overview: [Premo-Flex Cable Jumpers](#)
Description: 0.50mm Pitch Premo-Flex FFC Jumper, Opposite Side Contacts (Type D), 178.00mm Cable Length, Tin (Sn) Plating, 32 Circuits

Documents:

Drawing (PDF)	Datasheet (PDF)
Product Specification PS-98266-001-001 (PDF)	RoHS Certificate of Compliance (PDF)
Packaging Specification PK-98266-001-001 (PDF)	

General

Product Family	Cable
Series	98266
Comments	Contacts on opposite sides, Type D
Crimp Quality Equipment	Yes
Overview	Premo-Flex Cable Jumpers
Product Name	Premo-Flex FFC Jumper
UPC	756054773062

Physical

Cable Length	178.00mm
Circuits (Loaded)	32
Material - Plating Mating	Tin
Net Weight	1.841/g
Packaging Type	Bag
Pitch - Mating Interface	0.50mm
Temperature Range - Operating	-40° to +105°C
Wire Size AWG	N/A
Wire/Cable Type	Flat Flex Cable

Electrical

Current - Maximum per Contact	0.5A
Voltage - Maximum	60V AC

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-98266-001-001
Product Specification	PS-98266-001-001
Sales Drawing	SD-98266-001



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China RoHS

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[98266](#) Series

Mates With

Easy-On FFC/FPC Connector:

[541043233](#) , [541323233](#) , [5019513200](#) ,
[525593233](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION