







### (c) NOTES:

1. METALSHELLS: COPPER ALLOY;  
min. 315µin TIN over 40-80µin NICKEL
2. INSULATOR: TPE
3. CLAMPS: STAINLESS STEEL
4. SCREW: STAINLESS STEEL

5. CONNECTOR IS PART MARKED: **PART NO. CONEC ABC**

| No. of pos. | A <sub>-0,76</sub> | B <sub>+0,25</sub> | C                                       | D <sub>-0,3</sub> | (d) E <sub>+25</sub> | (d) F <sub>-0,76</sub> | Part No.:<br>Bulk package | Part No.: (e)<br>Single package |
|-------------|--------------------|--------------------|-----------------------------------------|-------------------|----------------------|------------------------|---------------------------|---------------------------------|
| 9           | 31,19              | 16,79              | 25,00 <sup>+0,12</sup> <sub>-0,10</sub> | 6,12              | 8,23                 | 12,93                  | 165X14719X                | 165X14719XE                     |
| 15          | 39,52              | 25,12              | 33,30 <sup>+0,15</sup>                  | 6,12              | 8,23                 | 12,93                  | 165X14729X                | 165X14729XE                     |
| 25          | 53,42              | 38,84              | 47,04 <sup>±0,13</sup>                  | 5,99              | 8,23                 | 12,93                  | 165X14739X                | 165X14739XE                     |
| 37          | 69,70              | 55,30              | 63,50 <sup>+0,13</sup> <sub>-0,11</sub> | 5,99              | 8,23                 | 12,93                  | 165X14749X                | 165X14749XE                     |
| 50          | 67,31              | 52,68              | 61,10 <sup>+0,14</sup> <sub>-0,11</sub> | 5,99              | 10,95                | 15,75                  | 165X14759X                | 165X14759XE                     |

THIS DRAWING MAY NOT BE COPIED OR  
REPRODUCED IN ANY WAY, AND MAY NOT  
BE PASSED ON TO A THIRD PARTY WITHOUT  
WRITTEN PERMISSION.  
OWNERSHIP AND COPYRIGHT OF CONEC GmbH

DO NOT ALTER CAD DRAWING BY HAND

|       |             |            |        | tolerance |          | dim. in mm     |  |
|-------|-------------|------------|--------|-----------|----------|----------------|--|
| 1 x e | Ä4033       | 30.06.2011 | K.H.   | drawn     | 10.09.01 | E.Mickenbecker |  |
| 3 x d | Ä3662       | 23.08.2010 | K.H.   | appd.     | 10.09.01 | A.Mickenbecker |  |
| 1 x c | Ä1912       | 06.04.2004 | Lehmen | d-old     |          |                |  |
| 3 x b | Ä1788       | 06.06.2004 | Lehmen |           |          |                |  |
| a     | Origin      |            |        |           |          |                |  |
| rev.  | description | date       | name   |           |          |                |  |

**CONEC**®

|           |                                                                                  |        |  |
|-----------|----------------------------------------------------------------------------------|--------|--|
| scale:    | 2:1                                                                              |        |  |
| material: | SEE NOTES                                                                        |        |  |
| title:    | HOOD 9 - 50pos.<br>FOR SOCKET CONNECTOR<br>water resiatant, shielded for EMI/RFI |        |  |
| dwg no:   | Inventor 10                                                                      | DIN-A4 |  |
|           | 16K1A291A                                                                        | sh: 1  |  |
| part no:  | SEE TABLE                                                                        |        |  |