


BALL-ENDED HEXAGON DRIVERS

 **Chrome Vanadium**

4719

Order Ref	Size	mm	inch	mm	inch	mm	inch	mm	inch	g
T4719 03	3	100	4	4	1/8	80	3 1/4	180	7	34
T4719 04	4	100	4	5	1/4	80	3 1/4	180	7	42
T4719 05	5	100	4	6	1/2	90	3 1/2	190	7 1/2	62
T4719 06	6	125	5	7	1/2	90	3 1/2	215	8 1/2	80
T4719 08	8	150	6	10	1/2	100	4	250	10	157
Box Qty	6									

ENGINEER'S SCREWDRIVERS - SLOTTED

 **Chrome-Vanadium**

4720

Order Ref	mm	x	inch	mm	inch	mm	inch	mm	inch	mm	inch	g
T4720 075	75	x 5	3 x 1/4	0.8	0.3	5	1/4	90	3 1/2	165	6 1/2	48
T4720 106	100	x 6	4 x 1/2	1.0	0.4	6	1/2	100	4	200	8	73
T4720 1506	150	x 6.5	6 x 1/4	1.2	.05	6	1/2	100	4	250	10	84
T4720 1508	150	x 8	6 x 1/4	1.2	.05	7	1/2	110	4 1/4	260	10 1/4	114
T4720 2006	200	x 6.5	8 x 1/4	1.2	.05	6	1/2	100	4	300	12	93
T4720 2008	200	x 8	8 x 1/4	1.2	.05	7	1/2	110	4 1/4	310	12 1/4	126
T4720 02010	200	x 10	8 x 1/4	1.6	.06	9	1/2	110	4 1/4	310	12 1/4	181
T4720 2509	250	x 9.5	10 x 1/4	1.6	.06	8	1/4	110	4 1/4	360	14 1/4	170
Box Qty:	6											

DIN 5263, DIN 5264A, DIN 5268/2, ISO 2380-1

PHILLIPS

 **Chrome-Molybdenum**

4722

Order Ref	Size	mm	inch	mm	inch	mm	inch	mm	inch	g
T4722 006	PH0	x 60	2 1/4	3.5	1/4	70	2 1/4	130	5 1/4	22
T4722 015	PH0	x 150	6	3.5	1/4	70	2 1/4	220	8 1/4	28
T4722 108	PH1	x 80	3 1/4	5.0	1/4	90	3 1/2	170	6 1/4	48
T4722 115	PH1	x 150	6	5.0	1/4	90	3 1/2	240	9 1/4	59
T4722 125	PH1	x 250	10	5.0	1/4	90	3 1/2	340	13 1/2	75
T4722 210	PH2	x 100	4	6.0	1/2	100	4	200	8	72
T4722 215	PH2	x 150	6	6.0	1/2	100	4	250	10	84
T4722 225	PH2	x 250	10	6.0	1/2	100	4	350	14	104
Box Qty	6									

DIN 5261, DIN 5262, DIN 5268/2

POZIDRIV/SUPADRIV*

 **Chrome-Vanadium**

4723

Order Ref	Size	mm	inch	mm	inch	mm	inch	mm	inch	g
T4723 006	PZD/SDVO	x 60	2 1/4	3.0	1/4	70	2 1/4	130	5 1/4	20
T4723 015	PZD/SDVO	x 150	6	3.0	1/4	70	2 1/4	220	8 1/4	24
T4723 108	PZD/SDV1	x 80	3 1/4	5.0	1/4	90	3 1/2	170	6 1/4	48
T4723 115	PZD/SDV1	x 150	6	5.0	1/4	90	3 1/2	240	9 1/4	59
T4723 125	PZD/SDV1	x 250	10	5.0	1/4	90	3 1/2	340	13 1/2	77
T4723 210	PZD/SDV2	x 100	4	6.0	1/2	100	4	200	8	74
T4723 215	PZD/SDV2	x 150	6	6.0	1/2	100	4	250	10	84
T4723 225	PZD/SDV2	x 250	10	6.0	1/2	100	4	350	14	107
Box Qty	6									

INSTRUMENT SCREWDRIVERS - SLOTTED

 **Chrome-Vanadium**

4725

Order Ref	mm	x	inch	mm	inch	mm	inch	mm	inch	mm	inch	g
T4725 050	50	x 3	2 x 1/4	0.5	0.2	3.0	1/4	70	2 1/4	120	4 1/4	19
T4725 0753	75	x 3	3 x 1/4	0.5	0.2	3.0	1/4	70	2 1/4	145	5 1/4	20
T4725 0755	75	x 5	3 x 1/4	0.8	.031	5.0	1/4	90	3 1/2	165	6 1/2	48
T4725 103	100	x 3	4 x 1/4	0.5	0.2	3.0	1/4	80	3 1/4	180	7	29
T4725 105	100	x 5	4 x 1/4	0.8	0.31	5.0	1/4	90	3 1/2	190	7 1/2	51
T4725 125	125	x 5	5 x 1/4	0.8	0.31	5.0	1/4	90	3 1/2	215	8 1/2	55
T4725 153	150	x 3	6 x 1/4	0.5	.02	3.0	1/4	80	3 1/4	230	9	32
T4725 155	150	x 5	6 x 1/4	0.8	0.31	5.0	1/4	90	3 1/2	240	9 1/4	60
T4725 203	200	x 3	8 x 1/4	0.5	0.2	3.0	1/4	80	3 1/4	280	11	34
T4725 205	200	x 5	8 x 1/4	0.8	0.31	5.0	1/4	90	3 1/2	290	11 1/2	66
T4725 255	250	x 5	10 x 1/4	0.8	0.31	5.0	1/4	90	3 1/2	340	13 1/2	75
Box Qty:	6											

DIN 5263, DIN 5264B, DIN 5268/2, ISO 2380-1

NUT SPINNERS

 **Chrome-Vanadium**

4734M

Order Ref	mm AF	SW	mm	inch	mm	inch	mm	inch	mm	inch	g
T4734M 025	2.5	130	5 1/4	6	1/2	90	3 1/2	220	8 1/4	67	
T4734M 03	3.0	130	5 1/4	6	1/2	90	3 1/2	220	8 1/4	67	
T4734M 035	3.5	130	5 1/4	6	1/2	90	3 1/2	220	8 1/4	68	
T4734M 04	4.0	130	5 1/4	6	1/2	90	3 1/2	220	8 1/4	69	
T4734M 045	4.5	130	5 1/4	6	1/2	90	3 1/2	220	8 1/4	68	
T4734M 05	5.0	130	5 1/4	6	1/2	90	3 1/2	220	8 1/4	70	
T4734M 055	5.5	130	5 1/4	6	1/2	90	3 1/2	220	8 1/4	72	
T4734M 06	6.0	130	5 1/4	6	1/2	90	3 1/2	220	8 1/4	72	
T4734M 07	7.0	130	5 1/4	7	1/2	100	4	230	9	100	
T4734M 08	8.0	130	5 1/4	7	1/2	100	4	230	9	101	
T4734M 09	9.0	130	5 1/4	7	1/2	100	4	230	9	103	
T4734M 10	10.0	130	5 1/4	7	1/2	100	4	230	9	106	
T4734M 11	11.0	130	5 1/4	8	5/16	100	4	230	9	124	
T4734M 12	12.0	130	5 1/4	8	5/16	100	4	230	9	128	
T4734M 13	13.0	130	5 1/4	8	5/16	100	4	230	9	130	

BA

4734

T4734 08	8 BA	130	5 1/4	6	1/2	90	3 1/2	220	8 1/4	68
T4734 06	6 BA	130	5 1/4	6	1/2	90	3 1/2	220	8 1/4	70
T4734 05	5 BA	130	5 1/4	6	1/2	90	3 1/2	220	8 1/4	73
T4734 04	4 BA	130	5 1/4	6	1/2	100	4	230	9	84
T4734 03	3 BA	130	5 1/4	7	1/2	100	4	230	9	99
T4734 02	2 BA	130	5 1/4	7	1/2	100	4	230	9	101
T4734 00	0 BA	130	5 1/4	8	1/4	100	4	230	9	110
Box Qty:	6									

DIN 475 Part 2