

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 130153-0059
Status: **Active**
Overview: Ground Fault Circuit Interrupter (GFCI) Products
Description: Super-Safeway® In-Line Industrial GFCI, Portable, Single Phase, Manual Reset, NEMA 5-15 Plug & Connector, 15A, 120V, 0.61m (2.0') Cord Length

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)
[Product Literature \(PDF\)](#)
[Product Literature \(PDF\)](#)

Agency Certification

UL E66308

General

Product Family	Power Distribution
Series	<u>130153</u>
Enclosure Rating	NEMA 3R
GFCI Reset	Manual
Mounting Style	Portable
Open Neutral Relay	Yes
Overview	<u>Ground Fault Circuit Interrupter (GFCI) Products</u>
Product Literature Order No	987650-7737, 987651-0452
Product Name	Super-Safeway™
Receptacle Type	N/A
Type	GFCI Industrial Duty, Single Phase
UPC	78678889760
Woodhead	Yes

Physical

Cord Diameter	10.92mm (.430")
Cord Grip Body Size	Internal Double C-Clamp
Cord Length	0.61m (2.0')
Feed-Thru	Yes
Flip Lid	No
Material - Housing	Nylon
Number of Receptacles	1
Packaging Type	Bag

Electrical

Cord Type	12/3 SJTW
Current - Maximum per Contact	15A
GFCI	Yes-In-line
Ground Continuity Monitor	No
NEMA Configuration	NEMA 5-15
Voltage - Maximum	125V

Material Info

Old Part Number	15052-1M
-----------------	----------



EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
130153Series