





ELECTRICAL SPECS:

1. LIFE: 10,000 INSERTION/WITHDRAWAL CYCLE MINIMUM
2. CONTACT RESISTANCE: 50m Ω MAXIMUM
3. INSULATION RESISTANCE: 1000m Ω MINIMUM
4. DIELECTRIC WITHSTANDING VOLTAGE: 500AC MAXIMUM
5. MAXIMUM RATING: 5A, 12V DC


Date	SYM	REVISION RECORD	AUTH	DR	CK
05/08/04	A	ADDED ELECTRICAL SPECS	T.B.	B.S.	



PANEL CUT-OUT



1



3

2

SCHEMATIC DIAGRAM

ITEM NO.	PART NAME	MATL. SPECIFICATION	Tolerance (Inches)	Memory Protection Devices, Inc. 200 Broad Hollow Road, Farmingdale, New York 11735		
1	PIN TERMINAL	0.4 THK BRASS, SILVER PLTD.	Decimal ±.5 (.020)		Scale	Drawn By B.S.
2	SLEEVE SPRING	0.2 THK PHOSPHORSCENT BRONZE, SILVER PLTD.				Approved By T.B.
3	BREAK TERMINAL	0.3 THK BRASS, SILVER PLTD.				
4	PIN (Ø2.1)	COPPER, NICKLE PLTD.	Fractional ± .8 (.030)	Title DC JACK - PANEL MOUNT TYPE		
5	HOUSING	BLACK, P.B.T.	Angular ± 3°	Date 05/08/04	Drawing Number EJ504A	
6	INSULATOR	BAKELITE, NATURAL				