



PANEL CUT OUT



	inches	
	Maxi	mini
A	.290	.284
B	.262	.256



NOTES:

MATERIALS:

- CONTACT & SPRING = BERYLLIUM COPPER PER ASTM B196, ALLOY C17300, TEMPER TD04.
- INSULATORS = VIRGIN WHITE TEFLON PER ASTM D1710, GRADE 1, TYPE I, CLASS "B".
- LOCKWASHER = PHOSPHOR BRONZE PER ASTM B139, COPPER ALLOY C53400, TEMPER H04.
- ALL OTHER METAL PARTS = BRASS PER ASTM B16, ALLOY C36000, TEMPER H02.

FINISHES:

- CONTACT = GOLD PLATE PER ASTM B488-11, TYPE II, 50μin MIN, GRADE C, OVER 100 TO 200μin STRESS FREE SULFAMATE NICKEL PER AMS-QQ-N-290.
- SPRING = NICKEL PLATE PER AMS-QQ-N-290, CLASS 1, GRADE G, EXCEPT 100 TO 200μin THICK OVER 50 TO 100μin THICK COPPER PER AMS 2418.
- ALL OTHER METAL PARTS = GOLD PLATE PER ASTM B488-11, TYPE II, 30μin MIN, GRADE C OVER 100 TO 200μin COPPER STRIKE PER AMS 2418.

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON		DWN:	DATE	 Property of Radiall This document cannot be reproduced or communicated to a third party without prior written permission of RADIALL.		
		C.E.	03/08/18			
DECIMAL	ANGLE	CHKD:	DATE	SLB STRAIGHT FEMALE PLUG BULKHEAD MOUNT CLAMP TYPE FOR .085 S/R & SIMILAR CABLES		
		D.N.	03/08/18			
		APVD:	DATE	SIZE A FSCM NO. 19505 DWG NO. 3028-1541-010 REV A		
		J.M.	03/08/18			
REFERENCE:		MATERIALS & FINISHES:		THIRD ANGLE PROJECTION		
ORIGINATED: C.E. DATE: 03/08/18		SEE NOTES		SCALE 5:1 SHEET 1 OF 1		

3028-1541-010