

191 Waukegan Rd, Ste 206
Northfield, IL 60093-2743

Phone: (847)441-2526

Fax: (847)441-2522

Email: relays@magnecraft.com


Item # 70-782EL14-1, 70-782EL14-1 Socket / 10 Amp Rating, 300 Volts

QUOTE

70-782EL14-1 Socket / 10 Amp Rating, 300 Volts

14 Pin Ice Cube, Logic Style, DIN Panel Mount with Elevator Terminals, Module Compatible.

This Item is Normally Stocked



[SPECIFICATIONS](#) · [ELECTRICAL RATING](#) · [TEMPERATURE](#) · [CONSTRUCTION](#) · [MISCELLANEOUS](#)
· [PRODUCT CERTIFICATIONS](#)

SPECIFICATIONS

Contact Configuration	4PDT
Number of Terminals	14
Mounting Style	Panel DIN rail

ELECTRICAL RATING

Nominal Current Rating	10 A
Nominal Voltage Rating	300 V

TEMPERATURE

Storage Range	- 40 to + 105 °C
---------------	------------------

CONSTRUCTION

Protection Category (Finger Safe)	IP 20
Internal Metal Tracks	Copper Alloy Zinc Plated
Terminals	Steel Zinc Plated
Screw Style	Combination Head
Screw Size	M3 mm
Screw Torque 3 mm (Maximum)	7 / 0.8 Lb-in / Nm
Wire Connection Method	Elevator
Terminal Layout	Logic
Base	Square

MISCELLANEOUS

Wire Size Capacity (Maximum), EN 60204-1, Solid Cu	14 / 16 (2) AWG, 2.5 / 1.5 (2) mm ²
Wire Size Capacity (Maximum), EN 60204-1, Stranded Cu	14 / 16 (2) AWG, 2.5 / 1.5 (2) mm ²
DIN Rail Mounting, EN 60715	35 mm
Chassis Mount Screw Torque	7 / 0.8 Lb-in / Nm
Flammability Rating	94V-0 Class
Body Color	Light Gray
DIN Locking Method	Red Plastic Locking Clip

PRODUCT CERTIFICATIONS

Agency Approvals	CE RoHS UL CSA
------------------	-------------------------