




Part number		nb of cont.	A	B	C	D	E	F	G
15 11 006	x601xxx	006	2.54	6.96	8.89	5.76	4.76	6.56	1.05
15 11 008	x601xxx	008	3.81	8.23	10.16	7.03	6.03	7.83	1.69
15 11 010	x601xxx	010	5.08	9.50	11.43	8.30	7.30	9.10	2.32
15 11 012	x601xxx	012	6.35	10.77	12.70	9.57	8.57	10.37	2.96
15 11 014	x601xxx	014	7.62	12.04	13.97	10.84	9.84	11.64	3.59
15 11 016	x601xxx	016	8.89	13.31	15.24	12.11	11.11	12.91	4.23
15 11 018	x601xxx	018	10.16	14.58	16.51	13.38	12.38	14.18	4.48
15 11 020	x601xxx	020	11.43	15.85	17.78	14.65	13.65	15.45	5.50
15 11 022	x601xxx	022	12.70	17.12	19.05	15.92	14.92	16.72	6.13
15 11 024	x601xxx	024	13.97	18.39	20.32	17.19	16.19	17.99	6.77
15 11 026	x601xxx	026	15.24	19.66	21.59	18.46	17.46	19.26	7.40
15 11 028	x601xxx	028	16.51	20.93	22.86	19.73	18.73	20.53	8.04
15 11 030	x601xxx	030	17.78	22.20	24.13	21.00	20.00	21.80	8.67
15 11 032	x601xxx	032	19.05	23.47	25.40	22.27	21.27	23.07	9.31
15 11 034	x601xxx	034	20.32	24.74	26.67	23.54	22.54	24.34	9.94
15 11 036	x601xxx	036	21.59	26.01	27.94	24.81	23.81	25.61	10.58
15 11 038	x601xxx	038	22.86	27.28	29.21	26.08	25.08	26.88	11.21
15 11 040	x601xxx	040	24.13	28.55	30.48	27.35	26.35	28.15	11.85
15 11 042	x601xxx	042	25.40	29.82	31.75	28.62	27.62	29.42	12.48
15 11 044	x601xxx	044	26.67	31.09	33.02	29.89	28.89	30.69	13.12
15 11 046	x601xxx	046	27.94	32.36	34.29	31.16	30.16	31.96	13.75
15 11 048	x601xxx	048	29.21	33.63	35.56	32.43	31.43	33.23	14.39
15 11 050	x601xxx	050	30.48	34.90	36.83	33.70	32.70	34.50	15.02
15 11 052	x601xxx	052	31.75	36.17	38.10	34.97	33.97	35.77	15.66
15 11 054	x601xxx	054	33.02	37.44	39.37	36.24	35.24	37.04	16.29
15 11 056	x601xxx	056	34.29	38.71	40.64	37.51	36.51	38.31	16.93
15 11 058	x601xxx	058	35.56	39.98	41.91	38.78	37.78	39.58	17.56
15 11 060	x601xxx	060	36.83	41.25	43.18	40.05	39.05	40.85	18.20
15 11 062	x601xxx	062	38.10	42.52	44.45	41.32	40.32	42.12	18.83
15 11 064	x601xxx	064	39.37	43.79	45.72	42.59	41.59	43.39	19.47
15 11 066	x601xxx	066	40.64	45.06	46.99	43.86	42.86	44.66	20.10
15 11 068	x601xxx	068	41.91	46.33	48.26	45.13	44.13	45.93	20.74
15 11 070	x601xxx	070	43.18	47.60	49.53	46.40	45.40	47.20	21.37
15 11 072	x601xxx	072	44.45	48.87	50.80	47.67	46.67	48.47	22.01
15 11 074	x601xxx	074	45.72	50.14	52.07	48.94	47.94	49.74	22.64
15 11 076	x601xxx	076	46.99	51.41	53.34	50.21	49.21	51.01	23.28
15 11 078	x601xxx	078	48.26	52.68	54.61	51.48	50.48	52.28	23.91
15 11 080	x601xxx	080	49.53	53.95	55.88	52.75	51.75	53.55	24.55
15 11 082	x601xxx	082	50.80	55.22	57.15	54.02	53.02	54.82	25.18
15 11 084	x601xxx	084	52.07	56.49	58.42	55.29	54.29	56.09	25.82
15 11 086	x601xxx	086	53.34	57.76	59.69	56.56	55.56	57.36	26.45
15 11 088	x601xxx	088	54.61	59.03	60.96	57.83	56.83	58.63	27.09
15 11 090	x601xxx	090	55.88	60.30	62.23	59.10	58.10	59.90	27.72
15 11 092	x601xxx	092	57.15	61.57	63.50	60.37	59.37	61.17	28.36
15 11 094	x601xxx	094	58.42	62.84	64.77	61.64	60.64	62.44	28.99
15 11 096	x601xxx	096	59.69	64.11	66.04	62.91	61.91	63.71	29.63
15 11 098	x601xxx	098	60.96	65.38	67.31	64.18	63.18	64.98	30.26
15 11 100	x601xxx	100	62.23	66.65	68.58	65.45	64.45	66.25	30.90

Performance Level	
PL1 : >500 mating cycles	2
PL2 : >250 mating cycles	6
PLS4 : min 0.06µm Au over 0.7+0.2µm PdNi	5

Packaging	
tape & reel with 280pcs per reel	000
samples	333

	All Dimensions in mm Original Size DIN A3		Scale 1 : 1		Free size tol.		Ref.						
							Sub.						
	All rights reserved		Created by ATIRIS		Inspected by DE VANSSAY		Standardisation HOFFMANN		Date 2013-02-15		State Final Release		
	Department EC PD - FR												
HARTING Electronics GmbH D-32339 Espelkamp			Title har-flex str. male 1.75mm, vacuum cover									Doc-Key / ECM-Nr. 100222442/UGD/001/C 50000059040	
			Type TB		Number 1511XXXX601_XXX							Rev. C	Page 1/1