



Search Results

Evaluate

- FAQ's
- Product Bulletins
- PDF-Opti-Core Fi ..
- Technical References
- PDF-OM3 Multimod ..

Design a Solution

- Catalog Cut Sheet
- PDF-FOIRZ02Y Pro
- Part Drawings
- PDF-Multimode 50 ..

How to Buy

- Bill of Material
- Favorite Products List
- Locate Distributor


Home > Product On-Line Catalog > Search Results >

Current refinements (click to remove) Search Tips [?](#)

☒ Text Search: 'FOIPX02Y'

Your search criteria matched only one product, shown below

FOIPX02Y



- Used in interconnect and horizontal installations for riser (OFNR), plenum (OFNP), and general-purpose environments
- Multimode (OM4, OM3, OM2, and OM1) and singlemode (OS1/OS2) fiber available
- Sheath markings provide positive identification, quality traceability, and length verification
- Colored buffers for ease of identification
- High quality buffering offers ease of stripping while maintaining optical performance
- Small diameter and flexible jackets allow for routing in tight spaces such as panels, cable trays, and fiber-to-the-desk (FTTD) applications
- Other diameters available to meet your application needs
- Opti-Core®10Gig™ Fiber Optic Cable is designed to support network transmission speeds up to 10 Gb/s for link lengths up to 300 meters for OM3 and 550 meters for OM4 with an 850nm source per IEEE 802.3ae 10 GbE standard; backward compatible for use with all 50/125µm system requirements

These products are available for sale in the Americas regions only. Contact Customer Service for minimum order quantities, availability, and additional product configurations. Options include diameters, jacket colors, flame ratings and premium optical performance grades.

▪ Part Number	FOIPX02Y
▪ RoHS Compliance Status	Compliant
▪ Note	FOIPX02Y replaces FOIPX02
▪ Part Description	2-fiber 10Gig™ 50/125µm (OM3) multimode plenum rated interconnect cable; 2.9mm dia., zip-cord.
▪ Product Type	Interconnect Cable
▪ Color	Aqua
▪ Length (ft.)	8202
▪ Length (m)	2500
▪ Fiber Compatibility	10GbE 50/125µm
▪ Fiber Type	Multimode
▪ Bend Radius (In.)	2.3
▪ Bend Radius (mm)	58
▪ CE Compliant	No
▪ Fiber Count	2
▪ Flammability Rating	Plenum (OFNP)
▪ Pricing Description	Fiber Plenum Zipcord 50µm 10Gig, Interconnect Cable 2 Fiber Count
▪ Temperature Rating	32 Degrees Fahrenheit – 122 Degrees Fahrenheit 0 Degrees Celsius – 50 Degrees Celsius
▪ Tensile Load (Lbs)	50
▪ Tensile Load (N)	220
▪ Weight (Kg)	55.5
▪ Min. Order UOM	FT
▪ Min. Order Qty.	3281
▪ BOM Qty. (# of Pkgs.)	0
▪ Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.