





COIL: @ +25° C  
 RESISTANCE 700 OHMS ± 10%  
 NOMINAL VOLTAGE 26.5 VDC  
 MUST OPERATE 13.5 VDC  
 MUST RELEASE 8.1 VDC MAX, 1.5 VDC MIN.

ENVIRONMENT:

VIBRATION 10 CPS TO 3000 CPS @ 30 g's  
 SHOCK 100 g's 6 ± 1 MS. DURATION  
 TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE & RELEASE 4 MS MAX.  
 CONTACT STABILIZATION 2.5 MS MAX.

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 2A  
 28 VDC RESISTIVE 100,000 OPERATIONS

DR. R.B. 2/2/95 CK. 2/2/95

COMMUNICATIONS  
 INSTRUMENTS, INC.

CUST. QPL  
 CUST. NO. M39016/6-107P

TYPE "HFW" RELAY

HFW1131K04P