

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1212020007](#)
Status: **Active**
Overview: mPm DIN Valve Connectors
Description: mPm DIN Valve Connector, Form B-11mm, External Thread, 2 Pole Plus Ground Terminal, 250V AC/DC, Transparent, Silicone Gasket

Documents:

Drawing (PDF)	Packaging Specification PK-121202-C22-001 (PDF)
Product Specification PS-121201-001-001 (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification STR-1251-001 (PDF)	

General

Product Family	Field Attachable / Accessories
Series	121202
Form	B - 11mm
IP Rating	IP65, IP67
Material - Contact	Brass
Overview	mPm DIN Valve Connectors
Product Name	mPm
Type	Field Attachable Connector
UPC	883906916244

Physical

Cable Diameter	N/A
Coupling Type	External Thread
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	N/A
Keyway	None
Material - Connector Body	Polyamide
Material - Coupling Nut	N/A
Material - Plating Mating	Silver
Net Weight	10.000/g
Orientation	90° Angle
Pitch - Mating Interface	11.00mm
Poles	2
Temperature Range - Operating	-40°C to +125°C
Wire Size AWG	N/A

Electrical

Current - Maximum per Contact	16.0A
Voltage - Maximum	250V AC/DC

Material Info

Engineering Number	C22200T0S
--------------------	-----------

Reference - Drawing Numbers

Packaging Specification	PK-121202-C22-001
Product Specification	PS-121201-001-001, STR-1251-001
Sales Drawing	SD-121202-001



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[121202](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION