


Material

Nickel plated brass



IG	H mm	 mm	S mm	Number
M 12 x 1,5	2,8	15	0,7	1.167.1200.50
M 16 x 1,5	2,8	19	0,7	1.167.1600.50
M 20 x 1,5	3,0	24	0,7	1.167.2000.50
M 25 x 1,5	3,5	30	0,7	1.167.2500.50
M 32 x 1,5	4,5	36	0,7	1.167.3200.50
M 40 x 1,5	5,0	46	0,7	1.167.4000.50
M 50 x 1,5	5,0	60	0,7	1.167.5000.50
M 63 x 1,5	6,0	70	0,7	1.167.6300.50
PG 9	2,8	18	0,7	1.167.0900.01
PG 11	3,0	21	0,7	1.167.1100.01
PG 13,5	3,0	23	0,7	1.167.1300.01
PG 16	3,0	26	0,7	1.167.1600.01
PG 21	3,5	32	0,7	1.167.2100.01
PG 29	4,0	41	0,7	1.167.2900.01
PG 36	5,0	51	0,7	1.167.3600.01
PG 42	5,0	60	0,7	1.167.4200.01
PG 48	5,5	64	0,7	1.167.4800.01

